


**Product: [29500T](#)**

VFD 300% Gnd, 3C+G #16 Str TC, XLPE Ins+PVC Grd, OS+TC Brd w/#16 TC Drain, Blk LSZH Jkt, 600V TC-ER 90C Dry/Wet 1000V Flexible Motor Supply Cable WTTC

[Request Sample](#)
**Product Description**

Belden 300% Ground Flexible VFD, 3 Conductor 16AWG (26x30) Tinned Copper, XLPE Insulation M4 Color Code+PVC Insulated Ground, Overall Beldfoil®+Tinned Copper Braid(85%) Shield w/16AWG Tinned Copper Drain, Black LSZH Outer Jacket, 600V TC-ER-LS 90C Dry/Wet 1000V Flexible Motor Supply Cable WTTC SUN RES DIR BUR

**Technical Specifications**
**Product Overview**

Suitable Applications: Variable Frequency Drives (VFD); AC Motor and Drive Systems; Human safety applications with flame or toxicity concerns (low smoke, zero halogen)

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	16 AWG	26x30	TC - Tinned Copper
Ground	1	16 AWG	26x30	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Color Code
Conductor(s)	XLPE - Cross-Linked Polyethylene (Thermoset)	0.046 in (1.2 mm)	Black and Numbered
Ground	PVC - Polyvinyl Chloride	0.046 in (1.2 mm)	Green/Yellow Stripe

**Outer Shield**

Shield Type	Material	Coverage
Tape	Tri-Laminate (Alum+Poly+Alum)	100%
Braid	Tinned Copper (TC)	85%

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter	Ripcord
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.063 in (1.6 mm)	0.534 in (13.6 mm)	Yes

Overall Cable Diameter (Nominal): 0.534 in (13.6 mm)

**Electrical Characteristics**
**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	3.914 Ohm/1000ft (12.84 Ohm/km)	29 pF/ft (95 pF/m)	53 pF/ft (170 pF/m)	63 Ohm	55%	18 Amps per Conductor at 30°C

**Voltage**
**UL Voltage Rating**

1000 V (TC, WTTC, UL Flexible Motor Supply Cable)

**Mechanical Characteristics**
**Temperature**
**UL Temperature**
**Operating**

**Bend Radius**

Stationary Min.	Installation Min.
6.4 in (160 mm)	6.4 in (160 mm)

Max. Pull Tension:	256 lbs (116 kg)
Bulk Cable Weight:	169 lbs/1000ft (251 kg/km)

**Standards and Compliance**

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance, Burial
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading, 1202, 383 Vertical Tray Flame Test (70,000 BTU)
NEC / UL Compliance:	Article 336, TC-ER-LS, WTTTC, UL Flexible Motor Supply Cable
ICEA Compliance:	S-95-658
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

**History**

Update and Revision:	Revision Number: 0.396 Revision Date: 09-07-2025
----------------------	--

**Part Numbers****Variants**

Item #	Color	Putup Type	UPC	Footnote
29500T 0101000	Black	Reel	612825136552	C
29500T 0106000	Black	Reel	612825136569	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.