



### Main

Device short name	XCSL
Enclosure type	Water resistant enclosure indoor/outdoor Dustproof enclosure indoor/outdoor Ice/sleet proof enclosure indoor/outdoor

### Complementary

Line Rated Current	10 A
[Us] rated supply voltage	24 V DC
Actuator	Key
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO staggered 2 NC
Depth	1.73 in (43.94 mm)
Enclosure material	metal
Height	7.64 in (194.06 mm)
Installation direction	Electromagnet connection left Actuator supply right
Key locking position	Front
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	3
Permissible voltage	300 V AC
Pilot light	LED orange

### Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
IP Degree of Protection	IP67
NEMA degree of protection	NEMA 1/2/3/4/12

### Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389118074408
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	11.02 in (28 cm)
Package 1 Weight	33.79 oz (958 g)
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	21.78 lb(US) (9.879 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------