

**Product: [31518](#)**


Lead Wire, #18 Str TC, Neoprene Ins, AWM 3044

[Request Sample](#)
**Product Description**

Low Temp Rubber Lead Wire, 18AWG (19x30) Tinned Copper, Neoprene Insulation, AWM 3044 CSA TYPE CL902 300V 90C

**Technical Specifications**
**Product Overview**

Suitable Applications:	internal wiring of appliances, oil resistance applications, motor lead systems
------------------------	--

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	18 AWG	19x30	TC - Tinned Copper

**Insulation**

Material	Nom. Thickness	Nom. Insulation Diameter
Neoprene	0.032 in (0.81 mm)	0.109 in (2.77 mm)

Overall Cable Diameter (Nominal): 0.109 in (2.77 mm)

**Electrical Characteristics**
**Electricals**

Nom. Conductor DCR	Max. Current
7.06 Ohm/1000ft	22.4 Amps per Conductor at 30°C

**Voltage**

UL Voltage Rating
300 V (AWM 3044)

**Mechanical Characteristics**
**Temperature**

UL Temperature	Operating
90°C	-30°C To +90°C

**Bend Radius**

Stationary Min.	Installation Min.
1.09 in (27.7 mm)	1.09 in (27.7 mm)

Max. Pull Tension: 24.7 lbs (11.2 kg)

Bulk Cable Weight: 10 lbs/1000ft

**Standards and Compliance**

Environmental Suitability:	Indoor, Outdoor, Oil Resistance
Sustainability:	CA Prop 65

Flammability / Reaction to Fire:	Horizontal flame
AWM Compliance:	AWM 3044
CEC / C(UL) Compliance:	CL-902
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## Product Notes

Notes: 24 Hours @ 300°F (149°C) ~ 8 Hours @ 325°F (163°C) ~ 15 Minutes @ 450°F (232°C)

## History

Update and Revision: Revision Number: 0.502 Revision Date: 09-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
31518 010500	Black	Reel	500 ft	612825142416	F
31518 0102000	Black	Reel	2,000 ft	612825142409	C 1
31518 0105000	Black	Reel	5,000 ft	612825142423	C I U Z
31518 0062000	Blue, Light	Reel	2,000 ft	612825142379	I U
31518 0065000	Blue, Light	Reel	5,000 ft	612825142386	C I U Z
31518 0015000	Brown	Reel	5,000 ft	612825142324	C I U Z
31518 005500	Green, Dark	Reel	500 ft	612825142355	F
31518 0055000	Green, Dark	Reel	5,000 ft	612825142362	C I U Z
31518 0025000	Red	Reel	5,000 ft	612825142331	C I U Z
31518 0095000	White	Reel	5,000 ft	612825142393	C I U Z
31518 0045000	Yellow	Reel	5,000 ft	612825142348	C I U Z

C - CRATE REEL PUT-UP., I - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'. U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE). Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN., 1 - FINAL PUT-UP LENGTH MAY VARY -20% TO +10% FROM LENGTH SHOWN., F - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.