




**Product:** [613948](#) 

Surveillance CCTV, RG-11 #14 BC, 95% BC Braid, CMP

## Product Description

Surveillance & CCTV Cable, RG11, Plenum-CMP, 14 AWG solid bare copper, foam FEP core, 95% bare copper braid, PVDF

## Technical Specifications

### Product Overview

Suitable Applications:	Surveillance, CCTV Camera
------------------------	---------------------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1

Conductor Count:	1
------------------	---

#### Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in

#### Outer Shield

Type	Material	Coverage [%]
Braid	Bare Copper (BC)	95%

#### Outer Jacket

Material	Nominal Diameter
PVDF - Polyvinylidene Fluoride	0.348 in

Weight:	0.935 lbs
---------	-----------

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
2.6 Ohm/1000ft	2.6 Ohm/1000ft	1.2 Ohm/1000ft	1.2 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
16.3 pF/ft

#### Inductance

Nominal Inductance
0.106 $\mu$ H/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.17 dB/100ft
10 MHz	0.4 dB/100ft
50 MHz	0.95 dB/100ft
100 MHz	1.4 dB/100ft
200 MHz	2.1 dB/100ft
400 MHz	3.4 dB/100ft
700 MHz	5 dB/100ft
900 MHz	6 dB/100ft
1000 MHz	6.5 dB/100ft

#### Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
84 ns/100m	1.22 ns/ft	83%

#### Unbalanced Crosstalk

Typical Unbalanced NEXT %	Typical Unbalanced FEXT %
	0.9 MHz
0.9 MHz	

#### Voltage

UL Voltage Rating
300 V RMS

#### Mated Connection

Frequency (MHz)
1

#### Temperature Range

UL Temperature Rating:	125°C
Operating Temperature Range:	-20°C To +125°C

#### Mechanical Characteristics

Bulk Cable Weight:	81 lbs/1000ft
Maximum Recommended Pulling Tension:	138 lbs
Minimum Bend Radius During Installation:	0.9 in
Minimum Minor Axis Bend Radius:	3.5 in

#### Dimensions (WxHxD)

Width	Height	Depth
1	0.97	1

#### Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
RG Type:	11
Series Type:	11

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Related Part Numbers

Non-Plenum Number:	513945
--------------------	--------

## Variants

Item #	Color	Put-Up Type	Length	UPC
613948 0091000	White	Reel	1,000 ft	612825173823

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## History

Update and Revision:	Revision Number: 0.408 Revision Date: 02-20-2026
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.