

## METRIC MEASUREMENT VERSION

73004W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles


 For more Information  
 please call

1-800-Belden1

**General Description:**

20 AWG stranded (10x30) bare copper conductors, PVC insulation, oil-resistant PVC jacket.

**Physical Characteristics (Overall)****Conductor**

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 3            | 20  | 10x30     | BC - Bare Copper   |

Total Number of Conductors: 4

**Ground Wire**

|                                  |                          |
|----------------------------------|--------------------------|
| Ground Wire (Y/N):               | Y                        |
| Ground Wire AWG:                 | 20                       |
| Ground Wire Stranding:           | 10x30                    |
| Ground Wire Conductor Material:  | BC - Bare Copper         |
| Ground Wire Insulation Material: | PVC - Polyvinyl Chloride |

**Insulation**

Insulation Material:

| Insulation Material      | Wall Thickness (mm) |
|--------------------------|---------------------|
| PVC - Polyvinyl Chloride | 0.559               |

Insulation Color Code Chart:

| Color        | Description           |
|--------------|-----------------------|
| Black        | Individually Numbered |
| Yellow/Green | Ground                |

**Outer Shield**

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded            |

**Outer Jacket**

Outer Jacket Material:

| Outer Jacket Material    | Nom. Wall Thickness (mm) |
|--------------------------|--------------------------|
| PVC - Polyvinyl Chloride | 0.889                    |

**Overall Cable**

Overall Nominal Diameter: 6.909 mm

**Mechanical Characteristics (Overall)**

|                                        |                        |
|----------------------------------------|------------------------|
| Storage Temperature Range:             | -40°C To +90°C         |
| Installation Temperature Range:        | Flexing: -5°C To +90°C |
| Bulk Cable Weight:                     | 113.103 Kg/Km          |
| Max. Recommended Pulling Tension:      | 137.894 N              |
| Min. Bend Radius/Minor Axis:           | 35.560 mm              |
| Min. Bend/Installation:                | 35.560 mm              |
| Min. Bend Radius (Continuous Flexing): | 35.560 mm              |
| Flex Cycle Rating:                     | 1 Million Flexes       |

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

|                                    |                            |
|------------------------------------|----------------------------|
| AWM Specification:                 | UL Style 2587 (600 V 90°C) |
| CSA Specification:                 | 600 V AWM I/II A/B         |
| EU Directive 2011/65/EU (ROHS II): | Yes                        |
| MIL Order #39 (China RoHS):        | Yes                        |

Other Specification: VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU (RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65



METRIC MEASUREMENT VERSION

73004W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

Flame Test

CSA Flame Test: FT1

Suitability

Suitability - Burial: Yes

Electrical Characteristics (Overall)

Nom. Inductance:

| Inductance (µH/m) |
|-------------------|
| 0.689             |

Max. Capacitance Conductor to Conductor:

| Freq. (MHz) | Capacitance (pF/m) |
|-------------|--------------------|
| 0.001       | 91.868             |

Nom. Conductor DC Resistance:

| DCR @ 20°C (Ohm/km) |
|---------------------|
| 35.107              |

Max. Operating Voltage - UL:

| Voltage |
|---------|
| 600V    |

Put Ups and Colors:

| Item #         | Putup    | Ship Weight | Color | Notes | Item Desc                 |
|----------------|----------|-------------|-------|-------|---------------------------|
| 73004W 008100  | 100 FT   | 9.500 LB    | GRAY  |       | 20AWG 10/30 4C UNSHIELDED |
| 73004W 0081000 | 1,000 FT | 80.000 LB   | GRAY  |       | 20AWG 10/30 4C UNSHIELDED |
| 73004W 008500  | 500 FT   | 41.500 LB   | GRAY  |       | 20AWG 10/30 4C UNSHIELDED |

Revision Number: 0    Revision Date: 09-27-2017

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.