


Product: [734C6](#) 



DS3/DS4 Central Office Coax, 6 x RG-59, 20 AWG Solid SC, Foil + 85% TC Braids, PVC Inner & Outer Jkts, CMR

Product Description

DS3/DS4 Central Office Coax, 6 Coaxes, RG-59, 20 AWG Solid Silvered Copper Conductor, PE Insulation, Foil + 85% Tinned Copper Braid Shields, PVC Inner and Outer Jackets, CMR

Technical Specifications

Product Overview

Suitable Applications:	Central office wiring, DS3/DS4 interconnect, 734/735 telecommunications systems, switchboard communications
------------------------	---

Construction Details

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
6	20 AWG	Solid	0.032 in	SC - Silvered Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene (Foam)	0.148 in (3.76 mm)	White

Insulation Table Notes:	Gas Injected
-------------------------	--------------

Inner Shield

Layer	Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		85%

Inner Shield Table Notes:	Tape bonded to dielectric
---------------------------	---------------------------

Inner Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.235 in (5.97 mm)

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.777 in (19.7 mm)

Overall Cable Diameter (Nominal):	0.777 in (19.7 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss

Frequency	Min. Return Loss
5-150 MHz	32 dB

Attenuation

Frequency	Max. Attenuation
-----------	------------------

1 MHz	0.28 dB/100ft
5 MHz	0.59 dB/100ft
10 MHz	0.8 dB/100ft
22.5 MHz	1.18 dB/100ft
50 MHz	1.82 dB/100ft
100 MHz	2.6 dB/100ft
150 MHz	3.22 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
10 Ohm/1000ft (33 Ohm/km)	2.4 Ohm/1000ft (7.9 Ohm/km)	16.8 pF/ft (55.1 pF/m)	75 Ohm	80%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-40°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
7.75 in (197 mm)	7.75 in (197 mm)

Max. Pull Tension:	362 lbs (164 kg)
Bulk Cable Weight:	235 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor
Flammability / Reaction to Fire:	UL1666 Vertical Shaft, FT4
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.182 Revision Date: 04-02-2026
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
734C6 0081000	Gray	Reel	1,000 ft	612825184331	C
734C6 0082000	Gray	Reel	2,000 ft	612825184348	C
734C6 0083000	Gray	Reel	3,000 ft	612825184362	