



Product: [7438W](#) 

MachFlex™, 6+1G C #14 Str BC, PVC-NYL Ins, TPE Jkt, 1000V WTTC, 600V TC-ER

 [Request Sample](#)

Product Description

MachFlex™ for High Flex, 6+1G Conductor 14AWG (41x30) Bare Copper, PVC-NYL Insulation, TPE Outer Jacket, 1000V WTTC, 600V TC-ER

Technical Specifications

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
	14	41x30	BC - Bare Copper	6
Ground Wire	14	41x30	BC - Bare Copper	1

Conductor Count: 7

Insulation

Material	Nominal Diameter
PVC/Nylon - Polyvinyl Chloride + Nylon	0.117 in

Color Chart

Number	Color
1	Black and Numbered
2	Black and Numbered
3	Black and Numbered
4	Black and Numbered
5	Black and Numbered
6	Black and Numbered
7	Green/Yellow

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
TPE - Thermoplastic Elastomer	0.487 in	0.047 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
2.5 Ohm/1000ft

Voltage

UL Voltage Rating
1000 V RMS
600 V RMS

Temperature Range

UL Temperature Rating:	75°C Dry, 90°C Wet
Other Temp Range:	Flexing: -5°C To +90 °C

Mechanical Characteristics

Oil Resistance:	Yes
UV Resistance:	Yes
Flex Cycle Rating:	1 Million Flexes
Bulk Cable Weight:	162 lbs/1000ft
Maximum Recommended Pulling Tension:	469 lbs
Minimum Continuous Flexing Bend Radius:	4.9 in

Standards

NEC/(UL) Compliance:	TC-ER, W TTC
CEC/C(UL) Compliance:	CIC, TC
UL AWM Style Compliance:	AWM 20328
CSA AWM Compliance:	AWM I/II A/B

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	Yes - Oil Res II
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT4
IEEE Flammability:	IEEE 1202 FT4
UL voltage rating:	1000 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
7438W 060250	Chrome	Reel	250 ft	612825186663
7438W 0601000	Chrome	Reel	1,000 ft	612825186656
7438W 0605000	Chrome	Reel	5,000 ft	612825186670

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.373 Revision Date: 02-03-2025
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.