



Product: [7895A](#)

DeviceBus®, 2 Pr #18+20 Str TC, PVC+FPE Ins, IS+OA TC Brd, PVC Jkt, CMG, PLTC

 [Request Sample](#)

Product Description

DeviceBus® for ODVA DeviceNet™, 2 Pair 18+20AWG (19x30+19x32) Tinned Copper, PVC+Foam PE Insulation, Individual Beldfoil® & OA Tinned Copper Braid(65%) Shield, PVC Outer Jacket, CMG, PLTC

Technical Specifications

Product Overview

Suitable Applications: harsh environment, ODVA device-level communication, used with CIP (common Industrial Protocol) for control, configuration, and data collection between devices, such as sensors and actuators, and higher level devices such as PLC, and PC in industrial automation, bus topology, etc.

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Power Pair(s)	1	18 AWG	19x30	TC - Tinned Copper
Data Pair(s)	1	20 AWG	19x32	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Power Pair(s)	PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.080 in (2.0 mm)	Red & Black
Data Pair(s)	PE - Polyethylene (Foam)	0.040 in (1.0 mm)	0.129 in (3.28 mm)	Blue & White

Inner Shield

Element	Shield Type	Material	Coverage
Power Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%
Data Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Braid	Tinned Copper (TC)	65%	20 AWG (19x32) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.045 in (1.1 mm)	0.378 in (9.60 mm)

Outer Jacket1 Table Notes:	Jacket OD +/- 0.010
Overall Cable Diameter (Nominal):	0.378 in (9.60 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Max. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Power Pair(s)	6.9 Ohm/1000ft	6.9 Ohm/1000ft				4 Amps Per Conductor at 24 V (per NEC CL2) (Power Pair)
Data Pair(s)	10.9 Ohm/1000ft (35.8 Ohm/km)	10.9 Ohm/100m	12 pF/ft (39 pF/m)	120 Ohm	75%	

Nom Outer Shield DCR: 3.2 Ohm/1000ft (10 Ohm/km)

Voltage

UL Voltage Rating	
300 V (CMG, PLTC), 600 V (UL AWM 20201)	

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
3.8 in (97 mm)	3.8 in (97 mm)

Max. Pull Tension: 65 lbs (29 kg)

Bulk Cable Weight: 76 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEEE 1202, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CMG, PLTC
AWM Compliance:	AWM 20201
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
Other Standard Compliance(s):	ODVA Cable III

Product Notes

Notes: Mid. Meter marks on jacket to aid users in installation. ODVA DeviceNet is an Open DeviceNet Vendor Association, Inc. trademark.

History

Update and Revision: Revision Number: 0.550 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
7895A T5U500	Gray T5U	Reel	500 ft	612825190806	
7895A T5U1000	Gray T5U	Reel	1,000 ft	612825190790	C
7895A T5U5000	Gray T5U	Reel	5,000 ft	612825190813	C Z

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.