

# Product data sheet

## Characteristics

### XZCRA150941J2

Jumper cable XZ, male straight M12 4 pin, female straight M8 4 pin, PVC 2 m



#### Main

Accessory / separate part category	Cabling accessory
Accessory / Separate Part Type	Jumper cable

#### Complementary

Jumper cable end 1	M12 male 4 pins straight screw-on and clip-on
Jumper cable end 2	M8 female 4 pins straight screw-on and clip-on
Collar material	Metal
Cable composition	4 x 0.34 mm <sup>2</sup>
Cable length	6.56 ft (2 m)
Cable outer diameter	0.21 in (5.3 mm)
[Ue] rated operational voltage	60 V AC 75 V DC
Line Rated Current	4 A
Insulation resistance	>= 1000 MΩ
Maximum resistance across terminals	5000 mΩ
Net Weight	0.22 lb(US) (0.1 kg)

#### Environment

IP Degree of Protection	IP68
Ambient air temperature for operation	-13...185 °F (-25...85 °C) static

#### Ordering and shipping details

Category	22483-MACHINE CABLES
Discount Schedule	DS3
GTIN	3389119021654
Returnability	No
Country of origin	PL

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	5.51 in (14.0 cm)
Package 1 Weight	3.70 oz (105.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	40
Package 2 Height	5.91 in (15.0 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	10.33 lb(US) (4.685 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes


## Contractual warranty

Warranty	18 months
----------	-----------

---

Dimensions

---



---

Connections and Schemes

---

