

**MODEL:** CES-603318-24PM | **DESCRIPTION:** SPEAKER**FEATURES**

- cloth gasket
- 2 mounting flanges
- 65 mm lead wire
- connector

**SPECIFICATIONS**


| parameter               | conditions/description                                    | min | typ | max    | units    |
|-------------------------|-----------------------------------------------------------|-----|-----|--------|----------|
| input power             | max power: 1 minute on, 2 minutes off, 10 cycles          |     | 2.0 | 4.0    | W        |
| impedance               | at 1.0 kHz, 1.0 Vrms                                      | 3.4 | 4   | 4.6    | $\Omega$ |
| resonant frequency (Fo) | at 1.0 Vrms, 10 cm                                        | 640 | 800 | 960    | Hz       |
| frequency response      | as per IEC 268-5                                          | 200 |     | 20,000 | Hz       |
| sound pressure level    | at 2.0 W, 10 cm, avg at 1.0, 1.2, 1.5, 1.8 kHz            | 101 | 104 | 107    | dB       |
| distortion              | at 1.0 kHz, 1.0 Vrms, 10 cm                               |     |     | 5      | %        |
| buzz, rattle, etc.      | must be normal at sine wave, frequency range              |     |     | 2.83   | V        |
| polarity                | cone moves forward w/ positive dc current to "+" terminal |     |     |        |          |
| dimensions              | 60 x 33.0 x 17.8                                          |     |     |        | mm       |
| magnet                  | Nd-Fe-B                                                   |     |     |        |          |
| enclosure material      | ABS                                                       |     |     |        |          |
| cone material           | Cloth                                                     |     |     |        |          |
| terminal                | wire leads w/ connector                                   |     |     |        |          |
| weight                  |                                                           |     | 27  |        | g        |
| operating temperature   |                                                           | -20 |     | 60     | °C       |
| storage temperature     |                                                           | -30 |     | 70     | °C       |
| RoHS                    | yes                                                       |     |     |        |          |
| IP level                | IP66 (front side)                                         |     |     |        |          |

Notes: 1. All specifications measured at 15~35°C, humidity at 25~75%, under 86~106 kPa pressure, unless otherwise noted.

## MECHANICAL DRAWING

units: mm  
tolerance:  $\pm 0.5$  mm


wire: UL1571 28 AWG  
internal speaker: CMS-402811-28SP  
connector: JST GHR-02V-S-B



## RESPONSE CURVES


### Frequency Response Curve

Test Conditions: 2.83 Vrms / 10 cm



### Total Harmonic Distortion Curve

Test Conditions: 2.83 Vrms / 10 cm



REVISION HISTORY

| rev. | description                       | date       |
|------|-----------------------------------|------------|
| 1.0  | initial release                   | 11/05/2019 |
| 1.01 | added internal speaker details    | 03/12/2020 |
| 1.02 | updated datasheet                 | 04/06/2022 |
| 1.03 | logo, datasheet style update      | 08/05/2022 |
| 1.04 | CUI Devices rebranded to Same Sky | 09/11/2024 |
| 1.05 | updated datasheet                 | 03/19/2025 |

The revision history provided is for informational purposes only and is believed to be accurate.



Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

**sameskydevices.com**