



Product: [83048](#)



Lead Wire, #24 Str SPC, TFE Ins, AWM 1371

[Request Sample](#)

Product Description

High Temp Plastic Lead Wire, 24AWG (19x36) Silver Plated Copper, TFE Insulation, AWM 1371 105C TYPE ET MIL-W-16878/6 250V 200C

Technical Specifications

Product Overview

Suitable Applications: high temperature, inter-connection circuits, internal wiring of computer and electronic equipments, (Type ET) MIL-W-16878/6 applications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
24	19x36	SC - Silvered Copper	1

Conductor Count: 1

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PTFE - Polytetrafluoroethylene	0.036 in	0.006 in

Electrical Characteristics

Current

Max. Recommended Current [A]
Mil-Std-975M Table 3.16 (single wire): 3.3 A

Voltage

UL Voltage Rating
250 V RMS

Temperature Range

Non-UL Temp Rating:	200°C
UL Temperature Rating:	105°C

Mechanical Characteristics

Bulk Cable Weight:	3 lbs/1000ft
Minimum Minor Axis Bend Radius:	0.15 in

Standards

UL AWM Style Compliance:	AWM 1371
NEMA Compliance:	HP3
Military Compliance:	MIL-W-16878/6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes

EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length
83048 010100	Black	Reel	100 ft
83048 0101000	Black	Reel	1,000 ft
83048 001100	Brown	Reel	100 ft
83048 0011000	Brown	Reel	1,000 ft
83048 002100	Red	Reel	100 ft
83048 0021000	Red	Reel	1,000 ft

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'. S - STRIPING ADDERS FOR TYPES E AND EE: 1, 2, 3 STRIPES. MINIMUM ORDER 10,000' PER STRIPE COMBINATION. (SEE STRIPING ADDER TABLE)
-----------	--

History

Update and Revision:	Revision Number: 0.361 Revision Date: 02-03-2025
----------------------	--

© 2026 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.