

Product: [8761MN](#)

SpaceMaker™, 2 C #22 Str TC, PO Ins, OS, PVC Jkt, AWM 2937


[Request Sample](#)
Product Description

SpaceMaker™, 2 Conductor 22AWG (19x34) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, AWM 2937

Technical Specifications
Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	22 AWG	19x34	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.01 in (0.25 mm)	0.050 in (1.3 mm)	Black & White

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (19x36) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.135 in

Overall Cable Diameter (Nominal): 0.135 in

Electrical Characteristics
Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Inductance	Max. Current
18.1 Ohm/1000ft	28.8 pF/ft (94.5 pF/m)	55.9 pF/ft (183 pF/m)	51 Ohm	0.176 μ H/ft (0.577 μ H/m)	4.64 Amps per Conductor at 25°C
Nom Outer Shield DCR: 17.44 Ohm/1000ft (57.22 Ohm/km)					

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics
Temperature

UL Temperature	Operating
80°C	-20°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
1.350 in (34.29 mm)	1.350 in

Max. Pull Tension:	15.4 lbs (6.99 kg)
Bulk Cable Weight:	11 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
CPR Compliance:	CPR Euroclass: Eca
AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark

History

Update and Revision: Revision Number: 0.406 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	UPC
8761MN 006100	Blue, Light	612825386032
8761MN 0061000	Blue, Light	612825386049
8761MN 008100	Gray	612825386056
8761MN 0081000	Gray	612825382737
8761MN 004100	Yellow	612825386018
8761MN 0041000	Yellow	612825386025

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.