


Product: [9228](#)

93Ω RG-62A/U Type, #22 Sol BCCS, Semi-solid PE, BC Braid, HDPE Jkt, Burial

Product Description

Coax 93Ω RG-62A/U Type, 22 AWG solid bare copper-covered steel, semi-solid polyethylene insulation, bare copper braid shield (95% coverage), high-density polyethylene jacket, Burial

Technical Specifications
Product Overview

| | |
|------------------------|---------------------------|
| Suitable Applications: | Computer, Instrumentation |
|------------------------|---------------------------|

Construction Details

| | |
|----------|----|
| RG Type: | 62 |
|----------|----|

Conductor

| Size | Stranding | Nom. Diameter | Material |
|--------|-----------|---------------|----------------------------------|
| 22 AWG | Solid | 0.025 in | BCCS - Bare Copper Covered Steel |

Insulation

| Material | Nom. Insulation Diameter | Color Code | Notes |
|--------------------------------|--------------------------|------------|--|
| PE - Polyethylene (Semi-Solid) | 0.146 in (3.71 mm) | White | Solid PE monofilament spiral around conductor. Solid PE tube over monofilament |

Outer Shield

| Layer | Outer Shield Type | Material | Coverage |
|-------|-------------------|------------------|----------|
| 1 | Braid | Bare Copper (BC) | 95% |

Outer Jacket

| Material | Nom. Diameter |
|-------------------|--------------------|
| PE - Polyethylene | 0.242 in (6.15 mm) |

| | |
|-----------------------------------|------------------------------|
| Outer Jacket1 Table Notes: | Flooding grease under jacket |
| Overall Cable Diameter (Nominal): | 0.242 in (6.15 mm) |

Electrical Characteristics
Attenuation

| Frequency | Nom. Attenuation |
|-----------|------------------|
| 1 MHz | 0.25 dB/100ft |
| 10 MHz | 0.85 dB/100ft |
| 50 MHz | 1.90 dB/100ft |
| 100 MHz | 2.70 dB/100ft |
| 200 MHz | 3.80 dB/100ft |
| 400 MHz | 5.30 dB/100ft |
| 700 MHz | 7.30 dB/100ft |
| 900 MHz | 8.20 dB/100ft |
| 1000 MHz | 8.70 dB/100ft |

Electricals

| Nom. Conductor DCR | Nom. Outer Shield DCR | Nom. Capacitance Cond-to-Shield | Nom. Characteristic Impedance | Nom. Velocity of Prop. |
|--------------------|-----------------------------|---------------------------------|-------------------------------|------------------------|
| 41.2 Ohm/1000ft | 2.9 Ohm/1000ft (9.5 Ohm/km) | 13.5 pF/ft (44.3 pF/m) | 93 Ohm | 84% |

Voltage

Voltage Rating

300 V

Mechanical Characteristics

Temperature

Operating

-55°C to +80°C

Bend Radius

Installation Min.

2.4 in (61 mm)

Max. Pull Tension: 88 lbs (40 kg)

Bulk Cable Weight: 30 lbs/1000ft

Standards and Compliance

| | |
|--------------------------------|--|
| Environmental Suitability: | Outdoor - Aerial, Sunlight Resistance - Black only, Aerial - When supported by messenger wire |
| Sustainability: | CA Prop 65 |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

Update and Revision: Revision Number: 0.474 Revision Date: 09-07-2025

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC | Footnote |
|--------------|-------|------------|----------|--------------|----------|
| 9228 010500 | Black | Reel | 500 ft | 612825225539 | C |
| 9228 0101000 | Black | Reel | 1,000 ft | 612825225515 | C |
| 9228 0102000 | Black | Reel | 2,000 ft | 612825225522 | C |
| 9228 0105000 | Black | Reel | 5,000 ft | 612825225546 | C |

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.