



Product: [9366](#) 

High Perform Instr, 1 Tri #16 Str TC, PVC Ins E1, OS, PVC Jkt, PLTC

 [Request Sample](#)

Product Description

High Performance Instrumentation, 1 Triad 16AWG (19x29) Tinned Copper, PVC Insulation E1 Color Code, Overall Beldfoil® Shield, PVC Outer Jacket, PLTC

Technical Specifications

Product Overview

Suitable Applications:	Instrumentation, Sensors, Valves, Positioners, RTD, 4-20mA, 0-10V
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Triad(s)	1	16 AWG	19x29	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Triad(s)	PVC - Polyvinyl Chloride	0.019 in (0.48 mm)	0.097 in (2.5 mm)	Black, White, Red

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	18 AWG (19x30) TC

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter	Ripcord
PP - Polypropylene Tape	PVC - Polyvinyl Chloride	0.042 in (1.1 mm)	0.312 in (7.92 mm)	Yes

Overall Cable Diameter (Nominal):	0.312 in (7.92 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Inductance	Max. Current
Triad(s)	4.5 Ohm/1000ft	67 pF/ft (220 pF/m)	120.3 pF/ft (394.7 pF/m)	0.156 µH/ft (0.512 µH/m)	6.2 Amps per conductor at 25°C

Nom Outer Shield DCR:	5.14 Ohm/1000ft (16.9 Ohm/km)
-----------------------	-------------------------------

Voltage

UL Voltage Rating
300 V (PLTC, CMG)

Mechanical Characteristics

Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

Temperature Table Notes:	AWM 80°C
--------------------------	----------

Bend Radius

Stationary Min.	Installation Min.

3.0 in (76 mm)	3.0 in (76 mm)
----------------	----------------

Max. Pull Tension:	145 lbs (65.8 kg)
--------------------	-------------------

Bulk Cable Weight:	61 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance
----------------------------	--

Flammability / Reaction to Fire:	UL 1685 UL Loading, FT4, T-29-520, IEEE 1202
----------------------------------	--

CPR Compliance:	CPR Euroclass: Eca
-----------------	--------------------

NEC / UL Compliance:	Article 725, Article 727, Article 800, CMG, ITC, PLTC
----------------------	---

AWM Compliance:	AWM 2464
-----------------	----------

CEC / C(UL) Compliance:	CMG
-------------------------	-----

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	---

UK Regulation Compliance:	UKCA Mark
---------------------------	-----------

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

Product Notes

Notes:	Alternate color coding available upon request.
--------	--

History

Update and Revision:	Revision Number: 0.614 Revision Date: 04-10-2026
----------------------	--

Part Numbers

Variants

Item #	Color	UPC	Footnote
9366 0601000	Chrome	612825239536	
9366 0605000	Chrome	612825239543	Z
9366 060U500	Chrome	612825239529	

Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.