



SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS

RF Cable Assemblies Technical Data Sheet


PE338-200CM

Configuration

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: PE-P300LL

Features

- 83% Velocity of Propagation
- Shielding effectiveness > 95 dB
- Maximum VSWR is < 1.35:1 to 18 GHz
- Minimum Bend Radius of 1.5 inches
- Operating Temperature range of -55 to +125 °C
- ROHS and REACH Compliant
- Same day shipment of custom lengths
- 100% Continuity and RF tested



Description

The PE338 high performance test cable's 0.3 inch diameter and 83% phase velocity offer very low loss performance up to 18 GHz. The durable stainless steel connectors and FEP jacket provide a cost effective design ideal for test environments where a rugged cable assembly is required. The series is offered with Type N, TNC, and SMA connectors all rated to 18 GHz. A heavy Duty boot provides improved strain relief and adds to the durability of the cable assemblies. These cable assemblies are built using a double shielded flexible cable, providing excellent shielding effectiveness of greater than 95 dB. All PE338 cable assemblies are 100% Continuity and RF tested to published specifications. Custom lengths are built to order and shipped same day.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|------------|---------|--------------|
| Frequency Range | DC | | 18 | GHz |
| VSWR | | | 1.35:1 | |
| Velocity of Propagation | | 83 | | % |
| RF Shielding | 95 | | | dB |
| Capacitance | | 25 [82.02] | | pF/ft [pF/m] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS PE338-200CM](#)



SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE338-200CM

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|-------|-------|------|------|------|-------|
| Frequency | 1 | 2 | 4.5 | 9 | 18 | GHz |
| Insertion Loss (Max.) | 0.6 | 0.72 | 0.98 | 1.37 | 1.9 | dB |
| Insertion Loss (Typ.) | 0.53 | 0.66 | 0.85 | 1.18 | 1.63 | dB |
| Power Handling (Max.) | 1,800 | 1,200 | 900 | 650 | 400 | Watts |

Mechanical Specifications

Cable Assembly

Length*

78.74 in [200 cm]

Diameter

0.625 in [15.88 mm]

Cable

Cable Type

PE-P300LL

Impedance

50 Ohms

Inner Conductor Type

Solid

Inner Conductor Material and Plating

Copper, Silver

Dielectric Type

PTFE

Number of Shields

3

Shield Layer 1

Silver Plated Copper Tape

Shield Layer 2

Aluminum Polyester

Shield Layer 3

Silver Plated Copper Wire

Jacket Material

FEP, Green

Jacket Diameter

0.3 in [7.62 mm]

Repeated Minimum Bend Radius

1.5 in [38.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS PE338-200CM](#)



SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE338-200CM

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|------------------------------------|------------------------------------|
| Type | SMA Male | TNC Male |
| Specification | MIL-STD-348B | MIL-STD-348 |
| Impedance | 50 Ohms | 50 Ohms |
| Mating Cycles | 500 | 500 |
| Contact Material and Plating | Beryllium Copper, Gold over Nickel | Beryllium Copper, Gold over Nickel |
| Contact Plating Specification | 50 μ in minimum | 50 μ in minimum |
| Dielectric Type | PTFE | PTFE |
| Coupling Nut Material and Plating | Passivated Stainless Steel | Passivated Stainless Steel |
| Coupling Nut Plating Specification | SAE-AMS-2700 | SAE-AMS-2700 |
| Hex Size | 5/16 inch | 9/16 inch |
| Torque | 7 in-lbs [0.79 Nm] | 19 in-lbs [2.15 Nm] |
| Body Material and Plating | Passivated Stainless Steel | Passivated Stainless Steel |
| Body Plating Specification | SAE-AMS-2700 | SAE-AMS-2700 |

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or \pm 3/8", whichever is greater.

Environmental Specifications

Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS PE338-200CM](#)




SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE338-200CM

How to Order

Part Number Configuration:



Example: PE338-12 = 12 inches long cable
PE338-100cm = 100 cm long cable

SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to TNC Male Low Loss Test Cable 200 cm Length Using PE-P300LL Coax, RoHS PE338-200CM](#)


URL: <https://www.pasternack.com/sma-male-tnc-male-pe-p300ll-cable-assembly-pe338-200cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE338-200CM CAD Drawing

SMA Male to TNC Male Low Loss Test Cable 200 cm

Length Using PE-P300LL Coax, RoHS



NOTE:
LABEL FOR CABLE LENGTHS 48" OR SHORTER TO BE CENTERED, 48" OR LONGER WILL BE 12" AWAY FROM CONNECTOR.

PASTERNACK
THE ENGINEER'S RF SOURCE
Pasterнак Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasterнак.com | E-Mail: sales@pasternack.com

| DWG TITLE | PE338 |
|----------------|---------------------------------------|
| FSCM NO. 53919 | CAD FILE 062116 SCALE N/A SIZE A 2233 |

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES (mm).
4. LENGTH TOLERANCE IS $\pm 1.5\%$ OR 3/8", WHICHEVER IS GREATER.