

Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm
M17/176-00002-LC, 48" Cable



LC3MP2165-48

Configuration

- Connector 1: TRB 3-Slot Plug
- Connector 2: TRB 3-Slot Plug
- Cable Type: M17/176-00002-LC

Features

- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

L-com's LC3MP2165-48 is a bend relief 3-Slot TRB plug to plug for 78 Ohm M17/176-00002-LC, 48" cable and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 3-Slot to TRB 3-Slot cable assembly has a plug to plug gender configuration with 78 Ohm flexible M17/176-00002-LC series coax and operates to 10 MHz.

Custom versions of this TRB 3-Slot plug to TRB 3-Slot plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MP2165-48 L-com Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.256	0.284	0.312	0.34	0.38	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm
M17/176-00002-LC, 48" Cable



LC3MP2165-48

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.172 lbs [78.02 g]

Cable

Cable Type	M17/176-00002-LC
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug	TRB 3-Slot Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range	-55 to +200 deg C
-----------------	-------------------

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:


Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm
M17/176-00002-LC, 48" Cable



LC3MP2165-48

How to Order

Part Number Configuration:



Example: LC3MP2165-12 = 12 inches long cable
LC3MP2165-100cm = 100 cm long cable

Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable

L-com CAD Drawing

ZONE	REV	
		A

LABEL
SEE NOTE 1

M17176-00002, 78 OHM TWINAX CABLE
JACKET: FEP, BLUE
NOM. DIA. .129" [3.28]
www.L-Com.COM
LXXXXX

The diagram illustrates a coiled spring assembly. At the bottom, a cylindrical component labeled '2X TRB 3-LUG PLUG WITH BEND RELIEF' is shown. A horizontal line labeled 'LEN' extends from the left side of this component. Above the plug, a coiled spring is attached. A bracket on the left side of the spring is labeled '2X BEND RELIEF'. At the top of the spring, a rectangular component labeled 'W' is attached. A horizontal line extends from the right side of this top component.

NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
3. CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATE | C3MP2165-XX (XX = OAI IN INCHES)

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN () ARE MILLIMETERS	TOLERANCES.	FRACTIONS
	$X = \pm 2 [5]$	$\pm 1/32$
	$XX = \pm 02 [5]$	$\pm 1/16$
	$XXX = \pm 005 [1.3]$	$\pm 1/64$
		ANGLES $\pm 1^\circ$
		CABLE LENGTH TOLERANCES:
	$\pm 12 [305]$	$\pm 1.125 [30]$
	$\pm 120 [3050]$	$\pm 112.5 [305]$

BEND RELIEF 3-SLOT TRB PLUG TO PLUG FOR 78 OHM
M17176-0002 CABIE

REV
A
LC3MP2165
ITEM NO.
DRAWN BY
DMDY
CAGE CODE
43321
SIZE
A
LY
ES

IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS INC. ANY REPRODUCTION IN WHOLE OR IN PART, WHETHER BY MEANS OF MICROFILM, MICROFICHE, COMPUTER, OR ANY OTHER PROCESS, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS INC. IS PROHIBITED. THESE DRAWINGS ARE THE PROPERTY OF INFINITE ELECTRONICS INC. AND ARE TO BE RETURNED TO THE COMPANY UPON REQUEST. THESE DRAWINGS ARE THE PROPERTY OF INFINITE ELECTRONICS INC. AND ARE TO BE RETURNED TO THE COMPANY UPON REQUEST.