


**Product: [9510](#)**
**RS232, #24-10pr, SR-PVC, O/A Foil, PVC Jkt, CMG, 75Ω**
**Product Description**

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, 10 twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire (continued), PVC jacket.

**Technical Specifications**
**Product Overview**

**Suitable Applications:** RS-232 Applications; Computer Communications; Low Voltage Analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level Audio; Panel Wiring

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	10	24 AWG	7x32	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	SR-PVC - Polyvinyl Chloride (Semi-Rigid)	0.011 in (0.28 mm)	0.044 in (1.1 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green, Red & Blue

**Outer Shield**

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.034 in (0.86 mm)	0.368 in (9.35 mm)

Overall Cable Diameter (Nominal): 0.368 in (9.35 mm)

**Electrical Characteristics**
**Electricals**

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.	Max. Current
Pair(s)	28.8 Ohm/1000ft	30 pF/ft (98 pF/m)	50 pF/ft (160 pF/m)	60%	1.96 Amps per Conductor at 25°C

Nom Outer Shield DCR: 13.29 Ohm/1000ft (43.60 Ohm/km)

**Voltage**

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2464)

**Mechanical Characteristics**
**Temperature**

UL Temperature	Operating
80°C	-30°C to +80°C

**Bend Radius**

Stationary Min.	Installation Min.
3.7 in (94 mm)	3.7 in (94 mm)

Max. Pull Tension: 116 lbs (52.6 kg)

Bulk Cable Weight: 68 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464, AWM I/II A
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision: Revision Number: 0.479 Revision Date: 09-07-2025

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC/EAN	Footnote
9510.0030	Chrome	Reel	30 m	8719605021632	
9510 060100	Chrome	Reel	100 ft	612825254553	
9510.00152	Chrome	Reel	152 m	8719605021625	
9510.00305	Chrome	Reel	305 m	8719605021649	
9510 060500	Chrome	Reel	500 ft	612825254584	C
9510 0601000	Chrome	Reel	1,000 ft	612825254560	
9510 0602000	Chrome	Reel	2,000 ft	612825254577	C
9510 0605000	Chrome	Reel	5,000 ft	612825254591	C Z

Footnote: C - CRATE REEL PUT-UP., Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.