

Product: [9708](#) 



Speaker Cable, 2 Conductor 18 AWG, High Conductivity, Siamese

Product Description

Speaker Cable, 18 AWG stranded (16x30) ETP high-conductivity copper conductors, PVC insulation, parallel: (1) tinned, (1) bare.

Technical Specifications

Product Overview

Suitable Applications:	Speaker Cable
------------------------	---------------

Construction Details

Conductor

Size	Stranding	Material
18	16x30	TC - Tinned Copper (High Conductivity)
18	16x30	BC - Bare Copper

Insulation

Material
PVC - Polyvinyl Chloride

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.11 x 0.22 in

Electrical Characteristics

Voltage

Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

Operating
-20°C To +60°C

Max. Pull Tension:	50 lbs (23 kg)
Bulk Cable Weight:	19 lbs/1000ft (28 kg/km)

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.332 Revision Date: 09-07-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9708 368500	Clear, Transparent	Reel	500 ft	612825257134	
9708 368U500	Clear, Transparent	UnReel	500 ft	612825257172	
9708 3681000	Clear, Transparent	Reel	1,000 ft	612825257165	C
9708 368U1000	Clear, Transparent	UnReel	1,000 ft	612825257141	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.