


**Product: [9752](#)**

Electronic, 9 Pr #20 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)
**Product Description**

Electronic, 9 Pair 20AWG (7x28) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

**Technical Specifications**
**Product Overview**

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

**Construction Details**
**Conductor**

Element	No. of Elements	Size	Stranding	Material
Pair(s)	9	20 AWG	7x28	TC - Tinned Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.065 in (1.7 mm)	Black & Red, Black & White, Black & Green, Black & Blue, Black & Yellow, Black & Brown, Black & Orange, Red & White, Red & Green

**Outer Shield**

Material
No Shield

**Outer Jacket**

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.429 in

Overall Cable Diameter (Nominal): 0.429 in

**Electrical Characteristics**
**Electricals**

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
11.3 Ohm/1000ft	24.5 pF/ft (80.4 pF/m)	4.8 Amps per Conductor at 30°C

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**
**Temperature**

UL Temperature	Operating
80°C	-20°C to +80°C

**Bend Radius**

Stationary Min.	Installation Min.
4.29 in (109 mm)	4.29 in

Max. Pull Tension:	226.8 lbs (102.9 kg)
Bulk Cable Weight:	116 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2464
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.390 Revision Date: 09-07-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	UPC	Footnote
9752 060100	Chrome	612825258209	C
9752 0601000	Chrome	612825258216	C
9752 060500	Chrome	612825258223	C

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.