


Product: [9805](#)
RS232/422 Low Cap, #28-3pr, PP, O/A Foil+Braid, PVC Jkt, CL2, 100Ω
Product Description

Computer EIA RS-232/422 Cable, 3-Pair, 28 AWG stranded (7x36) tinned copper conductors, polypropylene insulation, overall Beldfoil® (100% coverage) + tinned copper braid shield (90% coverage), 28 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications
Product Overview

Suitable Applications:	RS-232 extended distance applications; RS-422 applications; computer communications; low voltage analog signals (4-20mA, 0-10V, ...); low voltage digital control (24V, ...); line level audio; panel wiring
------------------------	--

Construction Details
Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	3	28 AWG	7x36	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.009 in (0.23 mm)	0.033 in (0.84 mm)	Black & Red, Black & White, Black & Green

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	28 AWG (7x36) TC
Braid	Tinned Copper (TC)	95%	

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.035 in (0.89 mm)	0.222 in (5.64 mm)

Overall Cable Diameter (Nominal):	0.222 in (5.64 mm)
-----------------------------------	--------------------

Electrical Characteristics
Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Delay	Nom. Inductance	Nom. Velocity of Prop.	Max. Current
Pair(s)	73.5 Ohm/1000ft	16.5 pF/ft (54.1 pF/m)	27.5 pF/ft (90.2 pF/m)	100 Ohm	1.4 ns/ft	0.19 μH/ft (0.62 μH/m)	66%	0.9 Amps per Conductor at 25°C
Nom Outer Shield DCR: 5.7 Ohm/1000ft (19 Ohm/km)								

Voltage

UL Voltage Rating
30 V

Mechanical Characteristics
Temperature

UL Temperature	Operating
60°C	-30°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
2.2 in (56 mm)	2.2 in (56 mm)

Max. Pull Tension: 44 lbs (20 kg)

Bulk Cable Weight: 31 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, CL2
AWM Compliance:	AWM 2960
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision: Revision Number: 0.483 Revision Date: 09-07-2025

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
9805 060100	Chrome	Reel	100 ft	612825258780	
9805 060500	Chrome	Reel	500 ft	612825258803	C
9805 0601000	Chrome	Reel	1,000 ft	612825258797	C

Footnote: C - CRATE REEL PUT-UP.

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.