

AC Surge Protector SPD I2R DIN-Rail 240 Vac Single-Phase SASD 7 kA Status LED

1101-629



I2R ICP 240

Features

- 100% SASD Protection
- SASD and MOV Protection Options
- Visual Suppression Status Indicator
- DIN-Rail Mount

Applications

- Electrical Panelboards
- Industrial Automation
- Communications Base Stations
- IT & Data Centers
- Switchgear
- Motor Control Centers
- Automatic Transfer Switches
- Wastewater Treatment
- Oil & Gas
- LED Lighting
- Schools
- Hospitals

Description

AC surge protector (also known as SPD or lightning protector) 1101-629 from Transtector is a DIN-Rail style SPD that utilizes state of the art SASD technology to protect critical equipment that operates on a 240 Vac Single-Phase electrical service. This surge protector provides effective protection against electrical transient surges that are generated both by external lightning events and by internal switching events and supports long-term system reliability by safely shunting high amounts of transient energy while maintaining a very low clamping voltage. Transtector AC surge protectors are available in stock with same day shipping.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Service Voltages		240		Vac
Service Type		Single-Phase		
Frequency	50		60	Hz
Maximum Continuous Operating Voltage (MCOV) L - N			275	Vac
Maximum Continuous Operating Voltage (MCOV) L - G			275	Vac

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Surge Protection Technology		SASD		
Protection Modes		L-N/G		
8/20 μ s Surge Current			7	kA
Nominal Discharge Current Rating (In)		3		kA
V _{pl} 8/20 μ s L-N		600 @ 500A		Vpk
Response Time			5	ns

AC Surge Protector SPD I2R DIN-Rail 240 Vac Single-Phase SASD 7 kA Status LED

1101-629



Mechanical Specifications

Size

Height	2.6 in	[66.04 mm]
Width	1.03 in	[26.16 mm]
Depth	2.63 in	[66.8 mm]
Weight	0.4 lbs	[181.44 g]
Housing Material and Plating	Rynite FR350/PBT	

Environmental Specifications

Temperature Range (Operational)	-40 to +80 deg C
Humidity	90% non-condensing

Installation

Mount Type	DIN Rail
Service Wiring Terminal	#4 to #14

Compliance Certifications

Transtector Systems specializes in protection of highly sensitive, low voltage equipment through its patented, non-degrading silicon diode technology and custom filters. Our power quality expertise translates into a diverse product offering including AC, DC, and signal applications as well as integrated cabinets, power distribution panels and EMP hardened devices.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [AC Surge Protector SPD I2R DIN-Rail 240 Vac Single-Phase SASD 7 kA Status LED 1101-629](https://www.transtector.com/ac-surge-protector-spd-i2r-din-rail-240-vac-single-phase-sasd-7-ka-status-led-1101-629)

URL: <https://www.transtector.com/ac-surge-protector-spd-i2r-din-rail-1101-629>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Transtector reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Transtector does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Transtector does not assume liability arising out of the use of any part or document.

1101-629 CAD Drawing

AC Surge Protector SPD I2R DIN-Rail 240 Vac Single-Phase SASD 7 kA Status LED

