



Product: [9860](#)

Twinax 124Ω, 1 Pr #16 Sol BC, PO Ins, OA DF+TC Brd, PVC Jkt, CMX

 [Request Sample](#)

Product Description

Twinax 124Ω, 1 Pair 16AWG (Solid) Bare Copper, PO Insulation, Overall Duofoil®+Tinned Copper Braid(90%) Shield, PVC Outer Jacket, CMX

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
16	Solid	BC - Bare Copper	0.051 in	1

Conductor Count: 2

Insulation

Material	Nominal Diameter
PE - Polyethylene (Foam)	0.161 in

Color Chart

Number	Color
1	Blue & Clear

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		90%

Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.44 in	0.045 in

Construction and Dimensions

Stranding

Diameter
0.322 mm

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
4.2 Ohm/1000ft	1.3 Ohm/1000ft	1.3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
---	---	--------------------------------------

10.9 pF/ft

19.3 pF/ft

10.9 pF/ft

Inductance

Element	Nominal Inductance
(Loop)	(Loop) 0.24 μ H/ft

Impedance

Nominal Characteristic Impedance
124 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100m
10 MHz	0.7 dB/100m
50 MHz	1.8 dB/100m
100 MHz	2.9 dB/100m
200 MHz	4.1 dB/100m
400 MHz	6.2 dB/100m

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	1.3 ns/ft	78%

High Frequency

Frequency [MHz]
1 MHz
10 MHz
50 MHz
100 MHz
200 MHz
400 MHz

Voltage

UL Voltage Rating	Voltage Rating [V]
300 V RMS (CM)	AWM style 2448: 30 V RMS
300 V RMS (CMX)	

Temperature Range

UL Temperature Rating:	60°C
Operating Temperature Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	98 lbs/1000ft
Maximum Recommended Pulling Tension:	73 lbs
Minimum Minor Axis Bend Radius:	4.5 in

Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMX
CEC/C(UL) Compliance:	CMX
UL AWM Style Compliance:	AWM 2448
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (CM)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9860 010500	Black	Reel	500 ft	612825259725
9860 0101000	Black	Reel	1,000 ft	612825259701
9860 0102000	Black	Reel	2,000 ft	612825259718

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.487 Revision Date: 02-03-2025
----------------------	--

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.