

AC Surge Protector SPD CFS Brick 120/208/240 Vac 3-Phase Delta (Hi Leg) MOV 120 kA

A70-00-5011



LEA CFS 120/240-SPGD

Features

- High Capacity MOV Protection
- Suppression Status LEDs

Applications

- Electrical Panelboards
- Industrial Automation
- Communications Base Stations
- IT & Data Centers
- Switchgear
- Motor Control Centers
- Automatic Transfer Switches
- Wastewater Treatment
- Oil & Gas
- LED Lighting
- Schools
- Hospitals

Description

AC surge protector (also known as SPD or lightning protector) A70-00-5011 from Transtector is a brick style SPD that utilizes state of the art MOV technology to protect critical equipment that operates on a 120/208/240 Vac 3-Phase Delta (Hi Leg) electrical service. This surge protector provides effective protection against electrical transient surges that are generated both by external lightning events and by internal switching events and supports long-term system reliability by safely shunting high amounts of transient energy while maintaining a very low clamping voltage. Transtector AC surge protectors are available in stock with same day shipping.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Service Voltages		120/208/240		Vac
Service Type		3-Phase Delta (Hi Leg)		
Frequency	50		60	Hz
Maximum Continuous Operating Voltage (MCOV) H - L			276	Vac
Maximum Continuous Operating Voltage (MCOV) H - N			240	Vac

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Surge Protection Technology		MOV		
Protection Modes		L-N, L-L		
8/20 μ s Surge Current			120	kA
Response Time			25	ns

Mechanical Specifications

Size

Height	2.4 in	[60.96 mm].
Width	5.29 in	[134.37 mm]

AC Surge Protector SPD CFS Brick 120/208/240 Vac 3-Phase Delta (Hi Leg) MOV 120 kA

A70-00-5011



Depth	5.58 in	[141.73 mm]
Weight	5 lbs	[2.27 kg]
Housing Material and Plating	Plastic	

Environmental Specifications

Temperature Range (Operational)	-40 to +85 deg C
Environmental Protection Rating	NEMA 4X
Humidity	95% non-condensing

Installation

Mount Type	Panel
------------	-------

Compliance Certifications


Transtector Systems specializes in protection of highly sensitive, low voltage equipment through its patented, non-degrading silicon diode technology and custom filters. Our power quality expertise translates into a diverse product offering including AC, DC, and signal applications as well as integrated cabinets, power distribution panels and EMP hardened devices.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [AC Surge Protector SPD CFS Brick 120/208/240 Vac 3-Phase Delta \(Hi Leg\) MOV 120 kA A70-00-5011](#)

URL: <https://www.transtector.com/ac-surge-protector-spd-cfs-brick-120-a70-00-5011-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Transtector reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Transtector does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Transtector does not assume liability arising out of the use of any part or document.

A70-00-5011 CAD Drawing
AC Surge Protector SPD CFS Brick 120/208/240 Vac 3-Phase Delta (Hi Leg) MOV 120 kA



UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE MILLIMETERS		TRANSTECTOR 10701 AIRPORT ROAD, HAYDEN, ID 83835 PHONE: 1 208 635 6400 1 800 882 9110 FAX: 1 208 955 2041 www.transtector.com e-mail: sales@transtector.com	
TOLERANCES: .X±.2 [5.08] .XX±.01 [25] .XXX±.005 [13]	FRACTIONS ± 1/32 ± 1/16 ± 1/8	ANGLES ± 1°	ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.
THIRD-ANGLE PROJECTION	SIZE [CAGE]	DRAWN BY	PART NUMBER
⊕	A 30992	HMB	A70-00-5011
⊕	SCALE	1:2	REV
⊕	1	OF	A
THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF TRANSTECTOR CORPORATION. ALL RIGHTS RESERVED.			

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev A