

10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper

CA400LL003-10M




Configuration

- Connector 1: N Male
- Connector 2: N Female Bulkhead
- Cable Type: PPBC-400LL

Features

- LMR Equivalent Coax
- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Low Insertion Loss
- Double Shielded
- PE Jacket
- One Time Bend Radius of 1 Inch



Applications

- General Purpose
- Laboratory Use
- Antenna Installations
- Land Mobile Radio & Other Communication Systems
- Cellular & Wi-Fi Systems

Description

PolyPhaser CA400LL003-10M is a 10 meter Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper is built using high quality components by skilled technicians to ensure a reliable product. The Type N (M) and Type N (FBH) jumper connections are designed to industry standard interface dimensions to ensure superior performance. This product is in stock and available for same day shipping. Female bulkhead interfaces allow cables to be attached to a bracket to fix the cable and reduce unwanted movement. In addition, female bulkhead connectors are often used as an input/output to a piece of equipment or enclosure. This high-quality RF coaxial assembly is perfect in many RF Interconnect applications such as Wi-LAN, Land Mobile Radio (LMR), laboratory test and measurement, and many other RF systems. The CA400LL003-10M Type N to Type N cable assembly is the perfect companion to PolyPhaser line of RF surge protection devices particularly when used as an antenna jumper cable.

The 400 Series coax used in these Type N to Type N assemblies is a 0.4 inch diameter coax with a black PE jacket. This cable's foam Polyethylene dielectric is low loss material with a phase velocity of 85% reducing the attenuation when compared to solid dielectric coax cables. PolyPhaser Low Loss 400 Series coax has a solid center conductor and uses a double shield comprised of a wire braid over a foil tape construction which provides >90% shielding effectiveness. The construction and materials of the CA400LL003-10M result in a coax cable assembly with a 1 inch one time bend radius and a repeat bend radius of four inches. The cable assembly's combination of Type N to Type N Male/Female Bulkhead and 400 Series Low Loss Cable supports a maximum operating frequency of 5800 MHz. You can find detailed performance specifications in the product datasheet. Processes and procedures are in place to ensure products meet the published specifications.

For additional strength, these Type N Male to Type N Female Bulkhead cable assemblies have polyolefin heat shrink strain relief boots on both ends of the RF Cable Assembly Jumpers. The heat shrink booting uses a double walled epoxy filled material to prolong the life of the assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper CA400LL003-10M](#)

10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper

CA400LL003-10M



Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.3:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			1,500	Vrms
Jacket Spark			8,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Max.)	8.13	12.07	19.94	31.75	47.5	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. Insertion Loss is estimated as 0.15 dB per N male connector and 0.1 dB per N female connector.

Mechanical Specifications

Size

Length	393.7 in [10 m]
Diameter	0.405 in [10.29 mm]
Weight	2.26074 lbs [1.03 Kg]

Cable

Cable Type	PPBC-400LL
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.4 in [10.16 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper CA400LL003-10M](#)

10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper

CA400LL003-10M



Bending Moment	0.5 lbs-ft [0.68 N-m]
Tensile Strength	160 lbs [72.57 Kg]

Connectors

Description	Connector 1	Connector 2
Type	N Male	N Female Bulkhead
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Brass, Gold
Contact Plating Specification	70µ in. minimum	
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100µ in. minimum	

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
-----------------	------------------

Compliance Certifications

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

PolyPhaser protects and increases the reliability of global RF communications networks, including transportation, telecommunications, defense, security and industrial applications, with superior RF surge protection technologies including DC Block, DC Pass and Ultra Low PIM. Backed by responsive service and expert technical support PolyPhaser continually expands its product offering and services to serve engineers' urgent needs for RF components in mission critical communication networks.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 M Type N to Type N M/F Bulkhead 400 Series Low Loss Cable Jumper CA400LL003-10M](https://www.polyphaser.com/10-m-type-n-to-type-n-m-f-bulkhead-400-series-low-loss-cable-jumper-p.aspx)

URL: <https://www.polyphaser.com/10-m-type-n-to-type-n-m-f-bulkhead-400-series-low-loss-cable-jumper-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. PolyPhaser reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. PolyPhaser does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and PolyPhaser does not assume any liability arising out of the use of any part or documentation.

CA400LL003-10M CAD Drawing

