

25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper

CASPF375007-25FT




Configuration

- Connector 1: 7/16 DIN Female
- Connector 2: N Male
- Cable Type: SPF-375

Features

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- FRPE Jacket
- Shielding Effectivity > 100 dB
- 100% Tested with PIM Test Results Marked on Cable
- 1.25 Inch Minimum Bend Radius
- Low Loss with Excellent VSWR



Applications

- Distributed Antennas Systems (DAS)
- Fire Rated Installations
- Low PIM Applications
- Multi-Carrier Communication Systems

Description

PolyPhaser CASPF375007-25FT is a 25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper built using high quality components by skilled technicians to ensure a reliable product. The Type N Male to 7/16 DIN Female jumper connections are designed to industry standard interface dimensions to ensure superior performance. These low PIM corrugated cable assemblies are durable and fire rated for applications that require these parameters. All PolyPhaser cable assemblies are available for same day shipment to fulfill your urgent needs. This high-quality RF coaxial assembly is perfect in many RF Interconnect applications such as distributed antenna systems (DAS), fire rated installations, low PIM applications, and many other RF systems. The CASPF375007-25FT Type N to 7/16 DIN low PIM cable assembly is the perfect companion to PolyPhaser line of products, particularly when used as an antenna jumper.

The three eighths inch low PIM fire rated coax used in these Type N to 7/16 DIN assemblies is a .375 inch diameter copper corrugated coax with a black FRPE jacket. This cable's foam PE dielectric is low loss material with a phase velocity of 83% and offers excellent passive intermodulation (PIM) performance better than -160 dBc. The construction of the three eighths inch copper corrugated jumper results in a minimum bend radius of 1.25 inches. The cable assembly's combination of Type N to 7/16 DIN M/F and Times Microwave's SPF-380 low PIM plenum rated cable supports a maximum operation frequency of 5.8 GHz. Each cable assembly is installed with heat shrink booting on each end and a PIM label with the measured PIM level. You can find detailed performance specifications in the product datasheet. All PolyPhaser assemblies are tested and inspected prior to shipping.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper CASPF375007-25FT](#)

25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper



CASPF375007-25FT

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-158	dBc
Capacitance		24 [78.74]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Max.)	0.57	0.94	1.29	1.93	3.11	dB
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly.
The Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Size

Length	300 in [762 cm]
Diameter	1.14 in [28.96 mm]
Weight	3.528 lbs [1.6 Kg]

Cable

Cable Type	SPF-375
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	Foam PE
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube
Outer Conductor Material and Plating	Copper
Outer Conductor Diameter	0.38 in [9.65 mm]
Jacket Material	FRPE, Black
Jacket Diameter	0.435 in [11.05 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper CASPF375007-25FT](#)

25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper



CASPF375007-25FT

One Time Minimum Bend Radius 1.75 in [44.45 mm]

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Female	N Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Phosphor Bronze, Silver	Brass, Silver
Contact Plating Specification	200 µin	200 µin
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Brass, Tri-Metal
Outer Conductor Plating Specification		100 µin
Body Material and Plating	Brass, Tri-Metal	
Body Plating Specification	80 µin	
Coupling Nut Material and Plating		Brass, Tri-Metal
Coupling Nut Plating Specification		100 µin
Torque		9.74 in-lbs [1.1 Nm]

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Environmental Specification Notes:

CMR (Riser) Fire Rated

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper CASPF375007-25FT](#)

25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper



CASPF375007-25FT

Compliance Certifications

Plotted and Other Data

Notes:

PolyPhaser protects and increases the reliability of global RF communications networks, including transportation, telecommunications, defense, security and industrial applications, with superior RF surge protection technologies including DC Block, DC Pass and Ultra Low PIM. Backed by responsive service and expert technical support PolyPhaser continually expands its product offering and services to serve engineers' urgent needs for RF components in mission critical communication networks.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [25 FT Fire Rated Type N to 7/16 DIN M/F SPF-375 Low PIM Cable Jumper CASPF375007-25FT](https://www.polyphaser.com/25-ft-fire-rated-type-n-to-7-16-din-m-f-spf-375-low-pim-cable-jumper-p.aspx)

URL: <https://www.polyphaser.com/25-ft-fire-rated-type-n-to-7-16-din-m-f-spf-375-low-pim-cable-jumper-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. PolyPhaser reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. PolyPhaser does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and PolyPhaser does not assume any liability arising out of the use of any part or documentation.

CASPF375007-25FT CAD Drawing

