



**Product:** [DEIP164U](#) 

Indoor Digital Electricity Copper Cable, #16-4pr, TC, LS-PVC, CL4P, CMP, LS-PVC Jkt

## Product Description

Indoor Digital Electricity Copper Cable, 4-16 AWG Stranded (19x29) Tinned Copper Pairs with Flamarrest® insulation, Plenum-CL4P, CMP, Flamarrest® Jacket with Ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Digital Electricity™, Fault Managed Power Systems (FMPS), remote powering, indoor
------------------------	---

### Construction Details

#### Conductor

Size	Stranding	Material
16	19x29	TC - Tinned Copper

#### Insulation

Material	Nom. Thickness	Color Code
PVC - Polyvinyl Chloride	0.011 in (0.28 mm)	Black & Red, Black & White, Black & Green, Black & Blue

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.017 in (0.43 mm)	0.386 in (9.80 mm)

### Electrical Characteristics

#### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
4.3 Ohm/1000ft	30 pF/ft (98 pF/m)	7.5 Amps per Conductor at 25°C (35°C Temperature Rise)

#### Voltage

UL Voltage Rating
450 V RMS

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C	0°C To +75°C

Max. Pull Tension:	243 lbs (110 kg)
Bulk Cable Weight:	95 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	NFPA 262, FT6
NEC / UL Compliance:	Article 800, CL4P, CL3P
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE), REACH: 2019-05-14

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

## History

Update and Revision:	Revision Number: 0.77 Revision Date: 09-07-2025
----------------------	---

## Part Numbers

### Variants

Item #	Color	Length
DEIP164U	Apple Green	2,000 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.