

8 Way SMA Female Input Connector Power Divider, From 7 GHz to 12.4 GHz, Rated at 30 Watts



PE20DV1282

Features

- 8-Way Power Divider
- SMA Female Connectors
- 7 GHz to 12.4 GHz Frequency Range
- Max Power 30W (CW)
- Min Isolation 18 dB

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and reactive power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types. The PE20DV1282 is a 8 way power divider that operates from 7 to 12.4 GHz and can handle up to 30 Watts (CW). This SMA power divider offers 18 dB min isolation and 1.5:1 max VSWR. The package interface uses SMA Female inputs on all of the ports.

Electrical Specifications

Number of Output Ports 8

Description	Min	Typ	Max	Units
Frequency Range	7		12.4	GHz
Impedance		50		Ohms
Input VSWR		1.4:1	1.5:1	
Output VSWR		1.3:1	1.4:1	
Insertion Loss		0.8	1.2	dB
Isolation	18	20		dB
Amplitude Balance		±0.2	±0.6	dB
Phase Balance		±5	±9	Degrees
Nominal Power Splitting		9		dB
Input Power (CW)			30	Watts
Reverse Power (CW)			1	Watt
Input Power (Peak)			300	Watts

Mechanical Specifications

Size	
Length	2 in [50.8 mm]
Width	4 in [101.6 mm]
Height	0.5 in [12.7 mm]
Weight	0.1 lbs [45.36 g]
Finish	Grey Paint

8 Way SMA Female Input Connector Power Divider, From 7 GHz to 12.4 GHz, Rated at 30 Watts



PE20DV1282

Housing Material and Plating	Aluminum
Configuration	
Input Connector	SMA Female
Output Connectors	SMA Female

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C
Humidity	100% RH at 35°C, 95% RH at 40°C
Shock	20G for 11msec half sine wave, 3 axis both directions
Vibration	25g RMS (15 degrees) endurance, 1 hour per axis
Altitude	30,000 ft. (Epoxy Sealed controlled environment)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

8 Way SMA Female Input Connector Power Divider, From 7 GHz to 12.4 GHz, Rated at 30 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [8 Way SMA Female Input Connector Power Divider, From 7 GHz to 12.4 GHz, Rated at 30 Watts PE20DV1282](#)

URL: <https://www.pasternack.com/8-way-sma-power-divider-12.4-ghz-pe20dv1282-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE20DV1282 CAD Drawing

8 Way SMA Female Input Connector Power Divider, From 7 GHz to 12.4 GHz, Rated at 30 Watts



UNLESS OTHERWISE SPECIFIED, LEADING DIMENSIONS ARE IN INCHES, DIMENSIONS IN [] ARE MILLIMETERS		PE PASTERNAK® an INFINITI® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
TOLERANCES:		Website: www.Pasternack.com		SCALE	
X = ±.2 [5]		Phone: 1.866.727.8376 1.949.261.1920		NONE	
.XX = ±.02 [0.5]				SHEET	
.XXX = ±.005 [0.13]				1 OF 1	
ANGLES ± 1°					
CABLE LENGTH TOLERANCES:		DESCRIPTION			
<12 [305] ±.60 [15.24] = ±.2 [5.1] / -0		8 WAY SMA POWER DIVIDER FROM 7 GHz TO 12.4 GHz RATED AT 30 WATTS			
>12 [305] ≤ 60 [1524] = ±.4 [10.2] / -0					
>60 [1524] ≤ 120 [3048] = ±.4 [10.2] / -0					
>120 [3048] ≤ 300 [7620] = ±.6 [15.24] / -0					
>300 [7620] = ±.6 [15.24] / -0					
ALL DIMENSIONS ARE FOR REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, DIMENSIONS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.		SIZE		REV	
		A		A	
		CAGE CODE		ITEM NO.	
		53919		PE20DV1282	
		DRAWN BY			
		HBAKKE			

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW PROHIBITED.

PE D8 Rev-D4 Adda