

## Product: [OWL 4G North America](#)

LTE Ethernet Gateway, USA, Canada, VPN, Dual SIM, Serial, IO, Vehicles (E-Mark)



### Product Description

Industry 4.0 and Industrial IoT Cellular Router and Gateway. Optimized for 4G applications with edge pre-computing. VPN and openly programmable and extendable Linux. Rugged and approved for vehicles.

### Technical Specifications

#### Product description

Type:	OWL-L02.01-W00.00-F01-U01-A02-VXX.X.XX
Name:	OWL 4G North America
Description:	Industry 4.0 and Industrial IoT Cellular Router and Gateway. Optimized for 4G distributed applications with edge pre-computing. VPN and open extendable Linux.
Part Number:	942284001
Port Type and Quantity:	2x Ethernet, 2x Antenna, 2x SIM, 1x Power, 2x I/O, 2x Serial
Serial:	On 10-pin panel socket (connector included): RS485, RS232, Serial2TCP, Serial2UDP
Country certification:	USA, Canada
Processor:	ARMv7
Hard disk space:	Flash memory (512MB User data storage, 830MB User module storage)
RAM:	512MB

#### Product Life Cycle

Discontinuation Announcement Date:	2023-12-12
Last Order Date:	2024-06-01
Last Delivery Date:	2024-10-01
Last Service Date:	2029-12-01

#### More Interfaces

SIM Cards:	2x 2FF (3V, 1.8V), only one active at a time, can be configured independently, automatic switch on connection failure
Ethernet:	2x Ethernet: 10/100 Mbit/s (RJ45)
Power Supply:	Via 2-pin terminal block 3.5mm (included)
Signaling contact:	On 10-pin panel socket (connector included): Digital Input, Digital Output

#### Radio technology

Antenna connector:	2 x SMA Female (Cellular, Diversity)
Frequency band:	WCDMA: 850(Band 5) / 1700(Band 4) / 1900(Band 2) MHz, LTE (4G): 600(Band 71) / 700(Bands 12,13,14) / 850(Band 5) / 1700(Band 4,66) / 1900(Band 2) MHz
Transmission rate:	LTE Category 4: 150Mbps Download, 50 Mbps Upload

#### Power requirements

Current consumption:	Idle 2.5 W, Average 4 W, Maximum 11 W
Operating Voltage:	9 V DC to 36 V DC
Redundancy functions:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing), PPPoE bridge mode

#### Diagnostics features

Modules and components:	User modules as separate download: Lua, Python, NodeRED
-------------------------	---

Monitoring: Syslog (UDP) , SNMPv1/2c/3

## Security features

Authentication:	User Management (local, RADIUS, TACACS+, mixed)
Stateful inspection firewall:	Static Firewall IPv4/IPv6 with Incoming and Forwarding Ruleset, DoS protection

## Service

Other services:	DHCP Server (IPv4/IPv6, dynamic and static leases, IPv6 Prefix Delegation, DNS proxy) , DynDNS client , PPPoE , FTP server , E-Mail via SMTP , SMS (notifications and commands) , Telnet server
-----------------	---

## Software

Operating system:	Custom embedded Linux with Busybox Shell
VPN:	OpenVPN, IPSec, GRE, L2TP, PPTP
Switching:	VLAN (via Scripting), tunneled VLANs (via Scripting), IGMP
Management:	HTML5, SSH, SNMPv1/2c/3, Automatic configuration and firmware fetch from a web- or ftpserver, backup and restore with drag & drop
Diagnostics:	One click support report package, System log, Linux kernel log, reboot log, signal strength history (60 days), SSH linux shell, Signal strength LED indicators
Configuration:	Simple to edit text file configuration, HTTP, HTTPS, SMS, SSH, Telnet, 4 Configuration Profiles, automatic via web/ftp, SNMPv1/2c/3
Security:	HTTPS, SSH, Authentication with RADIUS or TACACS+, activate cellular interface with SMS, Ethernet 802.1X (EAP-PEAP/MsCHAPv2 or EAP-TLS)
Time synchronisation:	SNTP Client, SNTP Server , Battery for RTC (CR1225)
Routing:	Static unicast routing, Multinetting, IP masquerading, Port forwarding, Multiple routes with priority and load sharing, 1:1 NAT
Dynamic routing:	Dual VRRPv2 (with ping probes), Dual VRRPv3 (with ping probes), multiple routed interfaces (ping monitoring, failover and load balancing)

## Ambient conditions

MTBF (MIL-HDBK-217F-2, parts count):	55.2 Years
Degree of Protection when Installed:	IP30
Operating temperature:	-40-+65 °C
Minimum Storage Temperature:	-40-+85 °C
Relative humidity (non-condensing):	0-95 %

## Mechanical construction

Dimensions (WxHxD):	145x32x105 mm
Weight:	510 g
Housing:	Metal
Mount Type:	DIN Rail and Wall mounting
Protection class:	IP30

## Approvals

Safety of industrial control equipment:	UL/EN/AS/NZS 62368-1:2014 (formerly EN 60950-1)
Transportation:	E8 (vehicles) , EN 45545-1 (fire) , EN 45545-2 HL1/HL2/HL3
Radio:	PTCRB, AT&T, Verizon (pending), FCC CFR-47:2017 Part 15 Subpart B Class A, FCC CFR-47:2016 Part 22 Subpart H, FCC CFR-47:2016 Part 24 Subpart E

## Reliability

Guarantee:	60 months (please refer to the terms of guarantee for detailed information)
------------	---

## Scope of delivery and accessories

Accessories:	942042105 Indoor LTE Antenna , 942117001 50Ohm terminator for cellular antenna , 943662015 Rail Power Supply
Scope of delivery:	Device, DIN rail clip, wall mount wings, 2-pin power connector, 10-pin connector for I/O and RS232/RS485

## Further Instructions

Product Documentation:	<a href="https://www.doc.hirschmann.com">https://www.doc.hirschmann.com</a>
Certificates:	<a href="https://www.doc.hirschmann.com/certificates.html">https://www.doc.hirschmann.com/certificates.html</a>
Software Download:	<a href="https://my.belden.com/s/downloads">https://my.belden.com/s/downloads</a>

## History

Update and Revision:	Revision Number: 0.125 Revision Date: 11-06-2025
----------------------	--

## Variants

Item #	Type
942284001	OWL 4G North America

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.