



Product: [OZD Profi 12M P11](#)

New generation: interface converter electrical/optical for PROFIBUS-field bus networks; repeater function; for plastic FO; short-haul version; approval for Ex-zone 2 (Class 1, Div. 2)

Product Description

New generation: interface converter electrical/optical for PROFIBUS-field bus networks; repeater function; for plastic FO; short-haul version; approval for Ex-zone 2 (Class 1, Div. 2)

Technical Specifications

Product description

| | |
|-------------------------|---|
| Type: | OZD Profi 12M P11 |
| Name: | OZD Profi 12M P11 |
| Part Number: | 942148007 |
| Port Type and Quantity: | 1 x optical: 2 sockets BFOC 2.5 (STR); 1 x electrical: Sub-D 9-pin, female, pin assignment according to EN 50170 part 1 |
| Signal Type: | PROFIBUS (DP-V0, DP-V1, DP-V2 und FMS) |

More Interfaces

| | |
|--------------------|--------------------------------------|
| Power Supply: | 8-pin terminal block, screw mounting |
| Signaling contact: | 8-pin terminal block, screw mounting |

Network size - length of cable

| | |
|---|---|
| Multimode fiber HCS (MM) 200/230 μ m: | 400 m; 8 dB link budget at 660 nm and transmitting power default; $A = 8 \text{ dB/km}$, 2 dB reserve |
| Multimode fiber POF (MM) 980/1000 μ m: | 50 m; 15 dB link budget at 660 nm and transmitting power reduced; 80 m; 20 dB link budget at 660 nm and transmitting power default; $A = 0.2 \text{ dB/m}$, 2 dB reserve |

Power requirements

| | |
|-----------------------|----------------------------|
| Current consumption: | max. 190 mA |
| Input voltage range: | -7 V ... +12 V |
| Operating Voltage: | 18 ... 32 VDC, typ. 24 VDC |
| Power consumption: | 4.5 W |
| Redundancy functions: | redundant 24 V infeed |

Power Output

| | |
|--|---|
| Output voltage/output current (pin6): | 5 VDC $\pm 5\%$, -10%, short circuit-proof/10 mA |
|--|---|

Ambient conditions

| | |
|--|-------------|
| MTBF (Telcordia SR-332 Issue 3) @ 25°C: | 3 645 832 h |
| Operating temperature: | 0-+60 °C |
| Minimum Storage Temperature: | -40-+70 °C |
| Relative humidity (non-condensing): | 10-95 % |

Mechanical construction

| | |
|---------------------|----------------------|
| Dimensions (WxHxD): | 39.5 x 137.5 x 84 mm |
| Weight: | 560 g |

| | |
|-------------------|----------------------------|
| Housing Material: | die-cast zinc |
| Mount Type: | DIN rail or mounting plate |
| Protection class: | IP40 |

Approvals

| | |
|---|---|
| Basis Standard: | EU Conformity, FCC Conformity, AUS Conformity Australia |
| Safety of industrial control equipment: | cUL61010-2-201 |
| Hazardous locations: | ISA 12.12.01 Class 1 Div. 2, ATEX Zone 2 |

Reliability

| | |
|------------|---|
| Guarantee: | 60 months (please refer to the <a href="https://assets.belden.com/m/1424ddb7a3280e7a/original/Hirschmann-Automation-and-Control-GmbH-Terms-of-Guarantee.pdf" terms of guarantee </a for detailed information) |
|------------|---|

Scope of delivery and accessories

| | |
|--------------------|--|
| Scope of delivery: | device, 2 optical BFOC ST plugs, start-up instructions |
|--------------------|--|

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.