



Product: [B96572](#)
Tactical Cable OM1 6 Fibers

Product Description

FiberExpress Tactical Cable, 6-Fiber, OM1, with Black Jacket, Small & Lightweight, Ideal for repeated deployment and retrieval cycles, superior crush resistance.

Technical Specifications

Product Overview

Suitable Applications:	Outdoor
------------------------	---------

Fiber Specifications

Fiber Type:	OM1
Fiber Core Diameter:	62.5/125um
Fiber Buffer Material:	Thermoplastic
Fiber Buffer Diameter:	900 +35um/-50um
Fiber Count:	6
Fiber Color Coding:	TIA-598-D

Outer Jacket Specifications

Jacket Material:	PUR - Polyurethane
Nom. Diameter:	0.24
Outer Jacket Color:	Black
Outer Jacket Ripcord:	1

Optical Characteristics

Wavelength	850 nm	1300 nm
Max. Attenuation	3.5 dB/km	1.2 dB/km

Mechanical Characteristics

Minimum Bend Radius During Installation:	20x
Minimum Bend Radius During Operation:	10x
Max. Tensile Strength During Installation:	330 N (74 lbf)
Max. Tensile Strength During Operation:	150 N (34 lbf)

Temperature Range

Installation Temperature Range:	-55°C To +85°C
Operating Temperature Range:	-46C to +85C
Storage Temperature Range:	-70°C To +85°C

Standards and Compliance

Environmental Suitability:	Outdoor, Sunlight Resistance
----------------------------	------------------------------

History

Update and Revision:	Revision Number: 0.202 Revision Date: 09-26-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	UPC
B96572	Black	Reel	612825280309

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.