

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	20[mm]
Max. Air Flow:	17.6[CFM]
Max. Air Flow:	0.5[m3 per min]
Max. Static Pressure:	0.16[In H2O]
Max. Static Pressure:	40.5[Pa]
Fan Speed:	4400[RPM]
Noise:	31.5[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.11[A]
Input Power:	1.3[W]
Mass:	85[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	EOL