

Detailed Specifications

Frame Width:	200[mm]
Frame Height:	200[mm]
Frame Depth:	51[mm]
Max. Air Flow:	472[CFM]
Max. Air Flow:	13.37[m3 per min]
Max. Static Pressure:	2.124[In H2O]
Max. Static Pressure:	529[Pa]
Fan Speed:	4000[RPM]
Noise:	61[dB]
Life Expectancy:	40 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Speed Control:	PWM
Nominal Voltage:	24[V]
Operating Voltage - Lower:	18[V]
Operating Voltage - Upper:	30[V]
Current:	1.5[A]
Input Power:	36[W]
Mass:	1200[g]
IP Rating:	Non IP model
Tach / Locked Rotor Output:	Tach Output
Status:	Active