




APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO # | Description   | Date     | Appr |
|-----|-------|---------------|----------|------|
| -   |       | RELEASED      | 7/31/09  |      |
| A   |       | REVISED SPEC. | 05/15/12 |      |



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Nylon66, rated UL 94V-0  
Insulator color: Beige  
Contacts: Brass  
Plating: Tin over copper underplate overall.  
Electrical:  
Voltage Rating: 250V AC  
Current Rating: 3 Amps Max  
Dielectric Withstanding Voltage: 1000V AC for 1 minute.  
Insulation Resistance: 1000 Megohms Min  
Contact Resistance: 20 Milliohms Max  
Temperature Range: -40°C to 105°C  
Environmental:  
Lead free, RoHS compliant

Positions: 02 thru 20  
A = .098 [2.50] x No. of Spaces  
B = .098 [2.50] x No. of Spaces + .197 [5.00]

UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES  
.X ± .10  
.XX ± .020  
.XXX ± .015  
APPROVALS  
DRAWN  
CHECKED  
APPROVED

ADAM TECH  
909 Rahway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710  
TITLE  
.098 [2.50] PITCH WAFER, RIGHT ANGLE  
PCB TYPE  
SIZE  
PART NO.  
25SH-E-XX-TR  
REV.  
A

