





Rev	AWO #	Description	Date	Appr
-		RELEASED	9/08/08	

APPROVED: _____
DATE: _____ TITLE: _____



Recommended PCB Layout



SPECIFICATIONS:

Material:
Insulator: Hi-Temp Nylon, rated UL 94V-0
Insulator color: Black
Contacts: Brass
Plating:
Gold Flash over Nickel underplate on mating area, Tin over Copper underplate on SMT tails
Electrical:
Operating voltage: 250 VAC max.
Current rating: 1 Amp max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
Operating temperature: -55°C to +105°C
Environmental:
Lead free, RoHS compliant
Recommended soldering temp: 260°C for 5 seconds

A = .079 [2.00] x No. of Positions per row + .283 [7.20]
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

APPROVALS

DATE

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] BOX HEADER, STRAIGHT,
GOLD PLATED, SURFACE MOUNT

DRAWN	DY	9/08/08	SIZE	PART NO.	REV.
CHECKED			X	2BHR-XX-VSG-SMT	-
APPROVED			REF:	SCALE: NTS	SHEET 1 OF 1