






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/21/15	
A		UPDATE DRAWING	4/20/20	AY/KL



SECTION B-B



SECTION A-A

SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Thickness: 0.2mm

Plating:

Tin over Nickel underplate overall

Electrical:

Rated Voltage: 250 V AC/DC

Rated Current: 2.0 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Wire range: 24-30 AWG

Insulation O.D: 1.13~1.40mm

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN	AY	4/21/15
-------	----	---------

CHECKED	LW	4/21/15
---------	----	---------

APPROVED		
----------	--	--

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

CRIMP CONTACT, FOR 2CH-C3-XX-V0

SIZE

X

PART NO.

2CTC3-R

REV.

A

REF: S00019C

SCALE: NTS

SHEET 1 OF 1