





DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/27/25	
A		UPDATE SPEC.	3/31/25	LW1/AC
B		UPDATE SPEC.	4/29/25	WY/AC





View A
Sticker

Vehicle Connector
wiring diagram

Customer signature:

Control box
wiring diagram



Control box
Product labeling
LASER

Material:
Insulator: Thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Copper Alloy, Silver plated surface
Electrical:
Voltage rating: 240V
Current rating: 8A/10A/13A/16A
Resistance: R6 150Ω, R7 330Ω
Dielectric withstanding voltage: >2,500V
Mechanical:
Mechanical life: > 10,000 times
Insertion and Extraction force: < 100N
Temperature Rating:
-40°C to 55°C
Environmental:
Waterproof: IP67
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
	MM	ANGLE				
X.	± 0.30	± 1°				
.X	± 0.20					
.XX	± 0.10					
DRAWN	LW1	3/27/25	TITLE NACS PORTABLE CHARGER CABLE 8-16A, NEMA 5-15P			
CHECKED	AC	3/27/25				
APPROVED						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			SIZE X	PART NO. CA #EV-AC-16AP-A04-6.1M-A	REV B	
REF: S00217C			SCALE: NTS		SHEET 1 OF 1	