

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/7/19	



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze

Plating:

Gold flash over Nickel underplate overall

Mechanical:

Recommended wire range: 24–28 AWG

Packaging:

R = Tape and Reel

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 ØX ± .10
.XX ± .020 ØXX ± .015
.XXX ± .015 ØXXX ± .010

APPROVALS		DATE
DRAWN	AY	3/7/19
CHECKED	CK	3/7/19
APPROVED		
SIZE	PART NO.	REV.
X	DCS-01A-R	-
REF: S00298T	SCALE: NTS	SHEET 1 OF 1

ADAM
TECH
INTERCONNECTS 909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

D-SUB SOCKET CONTACT, 24-28 AWG
GOLD FLASH PLATED