





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/23/08	
A		ADDED DIM.	9/9/14	AY/MMW




Mounting Hole Details


Wire Size AWG	Positions				
	2	4, 6	8, 10	12~24	
#18	9A	8A	7A	6A	
#20	7A	6A	5A	5A	
#22	5A	4A	4A	4A	
#24	4A	3A	3A	3A	



18 POSITION




16 POSITION



14 POSITION




6 POSITION




4 POSITION




2 POSITION




8 POSITION




10 POSITION




12 POSITION



20 POSITION



22 POSITION



24 POSITION

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: Natural

Electrical:

Operating voltage: 600 VAC max

Current rating: See chart

Insulation resistance: 1000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1500 VAC for 1 minute

Mechanical:

Wire size: 18 Awg thru 24 Awg

Temperature Rating:

Operating temperature: -40°C to 105°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 24
A = .165 [4.20] X No. of Spaces per row
B = .165 [4.20] X No. of Positions per row + .047 [1.20]
C = .165 [4.20] X No. of Positions per row + .063 [1.60]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

PLUG HOUSING, DUAL ROW, .165 [4.20] PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES .X ± .10 .XX ± .020 .XXX ± .015 .XXX ± .015				Holes ØX ± .10 ØXX ± .015 ØXXX ± .010			
APPROVALS				DATE			
DRAWN				DY			
CHECKED							
APPROVED							
SIZE				PART NO.			
X				DMF-XX-W			
REF: S00123T				SCALE: NTS			
				SHEET 1 OF 1			