





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9427	RELEASED	3/06/09	
A	-	REDRAWN	7/11/11	



Recommended PCB Layout



Poles	Tolerance
2-6P	±.006 [0.15]
7-12P	±.008 [0.20]
13-18P	±.010 [0.25]
19-24P	±.012 [0.30]

SPECIFICATIONS:

Material: Insulator: Thermoplastic, rated UL 94V-0
Insulator color: Green
Contact: Copper Alloy, Tin plated.
Electrical: Operation voltage: 300 VAC
Current rating: 10 Amps
Mechanical: Withstanding Voltage: 1.6KV
Environmental: Operating temperature: -40°C to +115°C
Lead free, RoHS compliant.



Poles: 2 thru 24
A = .150 [3.81] X No. of Spaces + .197 [5.00]
B = .150 [3.81] X No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED INCHES		TITLE	
.X ±.10 ØX ±.10 .XX ±.020 ØXX ±.015 .XXX ±.015 ØXXX ±.010		.150 [3.81] PITCH, TERMINAL BLOCK, VERTICAL	
APPROVALS		DATE	
DRAWN DY		3/06/09	
CHECKED		SIZE PART NO.	
APPROVED		X EBS-XX-B-180	
REF: S00007T		SCALE: NTS	
SHEET 1 OF 1		REV. A	

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710