

2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts

PE20DV1263



Features

- 2-Way Power Divider
- 2.4mm Female Connectors
- 8 GHz to 54 GHz Frequency Range
- Max Power 20W (CW)
- Min Isolation 15 dB

Applications

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Description

Pasternack carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Pasternack's resistive and reactive power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types. The PE20DV1263 is a 2 way power divider that operates from 8 to 54 GHz and can handle up to 20 Watts (CW). This N-Type power divider offers 15 dB min isolation and 1.8:1 max VSWR. The package interface uses 2.4mm Female inputs on all of the ports.

Electrical Specifications

Number of Output Ports 2

Description	Min	Typ	Max	Units
Frequency Range	8		54	GHz
Impedance		50		Ohms
Input VSWR		1.5:1	1.8:1	
Output VSWR		1.5:1	1.6:1	
Insertion Loss		0.8	1.3	dB
Isolation	15	17		dB
Amplitude Balance		±0.15	±0.3	dB
Phase Balance		±4	±6	Degrees
Nominal Power Splitting		3		dB
Input Power (CW)			20	Watts
Reverse Power (CW)			0.5	Watts
Input Power (Peak)			200	Watts
10% Duty Cycle, 1 µSec PW				

Specifications by Frequency

Description	F1	F2	F3	Units
Frequency Range	8-12	12-54		GHz
Input VSWR, Max	1.8:1	1.6:1		
Output VSWR, Max	1.6:1	1.6:1		

2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts



PE20DV1263

Specifications by Frequency

Description	F1	F2	F3	Units
Insertion Loss, Max	0.7	1.3		dB
Isolation, Min	16	15		dB

Mechanical Specifications

Size

Length	0.5 in [12.7 mm]
Width	1 in [25.4 mm]
Height	0.2 in [5.08 mm]
Weight	0.1 lbs [45.36 g]
Finish	Grey Paint
Housing Material and Plating	Aluminum

Configuration

Input Connector	2.4mm Female
Output Connectors	2.4mm Female

Environmental Specifications

Temperature

Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C
Humidity	100% RH at 35°C, 95% RH at 40°C
Shock	20G for 11msec half sine wave, 3 axis both directions
Vibration	25g RMS (15 degrees) endurance, 1 hour per axis
Altitude	30,000 ft. (Epoxy Sealed controlled environment)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts



PE20DV1263

Typical Performance Data

2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts PE20DV1263](#)

URL: <https://www.pasternack.com/2-way-2.4mm-power-divider-54-ghz-pe20dv1263-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE20DV1263 CAD Drawing

2 Way 2.4mm Female Input Connector Power Divider, From 8 GHz to 54 GHz, Rated at 20 Watts

