


Rev	AWO #	Description	Date	Appr
-		RELEASED	1/11/05	
A		REDRAWN	08/15/13	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Contact: Brass

Plating:

Gold flash over Nickel underplate

Electrical:

Operating voltage: 250 VAC max

Current rating: 5 Amps max

Contact resistance: 20 mohms max initial

Mechanical:

Recommended wire range: 24–26 AWG

Temperature Rating:

Operating temperature: –65°C to +125°C

Packaging:

B = loose cut

R = tape and reel

Environmental:

Lead free, RoHS compliant



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

HIGH DENSITY D-SUB SOCKET CONTACT

24-26 AWG

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				HOLES			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	SS		1/11/05	SIZE			
CHECKED				PART NO.			
APPROVED				HDGS-01-X			
REF: S00087T				SCALE: NTS			
				SHEET 1 OF 1			