

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/7/05	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 04 thru 100
A = .050 [1.27] x No. of Positions Per Row
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	Ø.X	± .10								
.XX	± .020	Ø.XX	± .015								
.XXX	± .015	Ø.XXX	± .010								
APPROVALS				DATE							
DRAWN	SS	1/7/05		.050 [1.27] DUAL ROW PIN HEADER				TITLE			
CHECKED											
APPROVED											
SIZE		PART NO.									
X		HPH2-B-XX-UA									
REF:		SCALE: NTS		SHEET 1 OF 1				REV. -			

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.050 [1.27] DUAL ROW PIN HEADER

SIZE PART NO. HPH2-B-XX-UA

SCALE: NTS

SHEET 1 OF 1