

Fiber Optic Transceiver, SFP, 1550nm, ZX SMF
80km, 1000Base DDM, Alcatel 73XX



FXC-SFP-ZX-1G-A73

Features

- Operating Data Rate up to 1.25 Gbps
- Distance Range 80KM
- Single 3.3V Power Supply and TTL Logic Interface
- Pluggable SFP Duplex LC Connector
- Standard and Industrial Operating Temperature
- Compliant with Alcatel 73XX SFP Specification

Applications

- Telecom (Service Provider)
- Datacom
- Enterprise Networks
- Government
- Fiber to the home/business

Description

The L-com FXC-SFP-ZX-1G-A73 is an SFP form-factor transceiver, supporting 1G Ethernet rates. The L-com FXC-SFP-ZX-1G-A73 supports 80KM distance and it is Alcatel 73XX compliant transceiver. The L-com FXC-SFP-ZX-1G-A73 features digital diagnostics for performance monitoring of the transceiver. The L-com FXC-SFP-ZX-1G-A73 is one of thousands of fiber optic connectivity products available from L-com in-stock and ready to ship. Contact our knowledgeable technical support and sales staff for your answers on fiber optic connectivity or other L-com products.

Configuration

Data Rate	1 Gbps
Form Factor	SFP
Connector	LC
Connector Mode	Duplex
Mode	Single Mode
Distance	80 km
Mfg Platform Compatibility	Alcatel 73XX

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Wattage			1.04	W
Power Supply Voltage Vcc	3.15	3.3	3.45	V
Power Supply Current Icc			300	mA

Optical Specifications

Description	Minimum	Typical	Maximum	Units
TX Center Wavelength	1500	1550	1580	nm
TX Data Rate		1.25		Gbps
TX Spectral Width			1	nm
TX Average Output Power	0		5	dBm
TX Extinction Ratio	9			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[Fiber Optic Transceiver, SFP, 1550nm, ZX SMF 80km, 1000Base DDM, Alcatel 73XX FXC-SFP-ZX-1G-A73](#)

Fiber Optic Transceiver, SFP, 1550nm, ZX SMF
80km, 1000Base DDM, Alcatel 73XX



FXC-SFP-ZX-1G-A73

RX Center Wavelength	1260	1600	nm
RX Receiver Sensitivity	-24		dBm
RX Receiver Overload		-3	dBm

Environmental Specifications

Temperature

Operating Range

0 to +70 deg C

Storage Range

-40 to +85 deg C

Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

Fiber Optic Transceiver, SFP, 1550nm, ZX SMF
80km, 1000Base DDM, Alcatel 73XX

FXC-SFP-ZX-1G-A73



Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver, SFP, 1550nm, ZX SMF
80km, 1000Base DDM, Alcatel 73XX

FXC-SFP-ZX-1G-A73




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Fiber Optic Transceiver, SFP, 1550nm, ZX SMF 80km, 1000Base DDM, Alcatel 73XX from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

