

SPDT Electromechanical Relay Latching Switch,
Terminated, DC to 50 GHz, Up to 80W, 12V,
2M Lifecycles, Solder Terminal, 2.4mm



PE71S9027

Features

- Single Pole Double Throw
- DC to 50 GHz Frequency Range
- Isolation greater than 50 dB minimum
- 2M Cycle Min Operating Life
- +12 Volt DC
- 80 Watt average Power
- Latching Actuator
- Terminated Ports
- -25 to +70°C Operating Temperature
- Insertion Loss as low as 1.1 dB Max
- VSWR as low as 1.9:1 max
- 2.4mm Female RF connectors
- Solder Terminals for DC Control

Applications

- Aerospace & Defense
- Test & Measurement
- Microwave Radio Systems
- Military Commercial Communication Systems
- Research & Development
- SATCOM
- Wireless Communications
- Enterprise
- IOT

Description

The PE71S9027 is a Single Pole Double Throw (SPDT) electromechanical relay switch that operates across a wide frequency range of DC to 50 GHz and can handle up to 80 Watts of CW input power in a break before make condition. The 50 Ohm design is rated for 2M life cycles for high reliability operation and features a Latching actuator, which maintains its position without continuous power, reducing power consumption and ensuring stable operation even during power loss. Additional features include terminated ports which minimize signal reflections. Impressive performance includes insertion loss less than 1.1 dB maximum and isolation greater than 50 dB minimum. The Latching actuator requires +12 Vdc bias voltage, and operates over a temperature range of -25°C to +70°C. The rugged and compact package assembly supports 2.4mm Female connectors and terminal solder pins for DC Control.

Electrical Specifications (TA = +25°C, DC Voltage = 12 Vdc)

Switch Type	SPDT, Terminated
Actuator Type	Latching
Switching Sequence	Make Before Break
Polarity	Negative Common

Description	Min	Typ	Max	Units
Frequency Range	DC		50	GHz
Impedance		50		Ohms
Operating Voltage	10.2	12	13	Volts
Actuating Current @ 12 Volts		420		mA
VSWR			1.9:1	
Insertion Loss			1.1	dB
Isolation	50			dB
Input Power (CW)			80	Watts
Switching Time			10	ms

SPDT Electromechanical Relay Latching Switch,
Terminated, DC to 50 GHz, Up to 80W, 12V,
2M Lifecycles, Solder Terminal, 2.4mm



PE71S9027

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 6	6 to 18	18 to 26.5	26.5 to 40	40 to 50	GHz
VSWR, Max	1.3:1	1.5:1	1.7:1	1.9:1	1.9:1	
Insertion Loss, Max	0.3	0.5	0.7	0.8	1.1	dB
Isolation, Min	70	60	55	50	50	dB
Power In, Max (CW)	80	50	20	10	5	Watts

Electrical Specification Notes:
Average Power at 25°C per RF Path

SPDT Electromechanical Relay Latching Switch,
Terminated, DC to 50 GHz, Up to 80W, 12V,
2M Lifecycles, Solder Terminal, 2.4mm



PE71S9027

Mechanical Specifications

Size

Length	1.92 in [48.77 mm]
Width/Diameter	2.19 in [55.63 mm]
Height	0.56 in [14.22 mm]
Weight	0.05 lbs [22.68 g]
Package Type	Connectorized
Operating Life	2,000,000 Cycles

Connectors

RF Connector Type	2.4mm Female
RF Connector Specification	IEEE STD 287
Control Connector	Solder Pin

Mechanical Specification Notes:
Solder Pins: 250°C max/30sec.

Environmental Specifications

Temperature

Operating Range	-25 to +70 deg C
Storage Range	-40 to +85 deg C
Construction	Splashproof

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Values shown are typical at 25°C.

SPDT Electromechanical Relay Latching Switch, Terminated, DC to 50 GHz, Up to 80W, 12V, 2M Lifecycles, Solder Terminal, 2.4mm from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SPDT Electromechanical Relay Latching Switch, Terminated, DC to 50 GHz, Up to 80W, 12V, 2M Lifecycles, Solder Terminal, 2.4mm PE71S9027](#)

URL: <https://www.pasternack.com/spdt-electromechanical-relay-latching-switch-terminated-50-ghz-80w-12v-2.4mm-pe71s9027-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE71S9027 CAD Drawing

SPDT Electromechanical Relay Latching Switch, Terminated, DC to 50 GHz,
Up to 80W, 12V, 2M Lifecycles, Solder Terminal, 2.4mm

