





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/7/22	
A		UPDATE SPEC.	9/8/23	LH/RC



**SPECIFICATIONS:**

**Material:**  
 Insulator: PA66, rated UL 94V-0  
 Insulator Color: See Chart  
 Contacts: Copper Alloy, Tin Plated


**Electrical:**  
 Voltage rating: 600 VAC  
 Current rating: 30 Amp  
 Dielectric withstanding voltage: 2200 VAC for 1 minute

**Mechanical:**  
 Recommended Wire Size:  
 Solid: 24-10AWG (0.2-6.0mm<sup>2</sup>)  
 Stranded: 24-12AWG (0.2-4.0mm<sup>2</sup>)  
 Stripping Length: .394"~.472" (10-12mm)  
 Temperature Rating:  
 Operating temperature: -40°C to +105°C

**Environmental:**  
 Lead free, RoHS compliant.



**RECOMMENDED RAIL SIZE**  
 35.0mm X 7.5mm



REB-B 2 C -XX

CSA (Cross Sectional Area)
Solid/Stranded
Solid: 24-10 Awg (0.2-6.0mm <sup>2</sup> )
Stranded: 24-12 Awg (0.2-4.0mm <sup>2</sup> )

Color
OR=Orange
BU=Blue
GY=Gray
YG=Yellow/Green

ADAM-P/N	Color
REB-B2C-OR	ORANGE
REB-B2C-BU	BLUE
REB-B2C-GY	GRAY
REB-B2C-YG	YELLOW/GREEN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	∅X	±.10
.XX	± .020	∅XX	±.015
.XXX	± .015	∅XXX	±.010

DRAWN	WX	10/7/22
CHECKED	RC	10/7/22
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

**ADAM TECH**

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

TITLE		REV: A
DIN RAIL TERMINAL BLOCKS, GUV 2 HOLE, 24-10 AWG		
SIZE X	PART NO. REB-B2C-XX	
REF: S00067C	SCALE: NTS	SHEET 1 OF 1