


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/28/13	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms

Frequency range: 0–6 GHz

Working Voltage: 170 VRMS max.

Dielectric Withstanding Voltage: 500 VRMS min.

Contact Resistance: 5 Milliohms max. (Center Contact)

2.5 Milliohms max. (Outer Contact)

Insulator Resistance: 1000 Megohms min.

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

RF CONNECTOR, TYPE MMCM,
50 OHM, PCB MOUNT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				Holes			
.X	± .10	ØX	± .10	DATE			
.XX	± .020	ØXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS							
DRAWN	HR	11/28/13					
CHECKED	YC	11/28/13					
APPROVED							
				SIZE	PART NO.	REV.	
				X	RF12-30-T-00-50-G	-	
REF: S00054T				SCALE: NTS	SHEET 1 OF 1		