






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/27/07	
A		REDRAWN	11/04/10	
B		REMOVE NUT & WASHER	12/01/10	
C		UPDATE DRAWING	5/6/15	AY/KW



RECOMMENDED PANEL CUTOUTS

INSULATOR	POM	NONE
BODY	ZINC ALLOY	NICKEL
CONTACT	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:
Nominal Impedance: 75 ohms
Frequency range: DC~3G
VSWR: 1.3 Max
Working Voltage: 500 VRMS @ Sea level
Insulator Resistance: 5000 Megohms min.
Temperature Rating:
-55°C to +155°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

75 OHMS BNC R/A PCB/PANEL
MOUNT JACK, METAL BODY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				HOLES			
.X	± .10	Ø.X	± .10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010
APPROVALS				DATE							
DRAWN	SLS		12/27/07								
CHECKED											
APPROVED											
TITLE				SIZE				PART NO.			
REF: S00720C				X				RF1-01-P-00-75-M			
SCALE: NTS								REV. C			
SHEET 1 OF 1											