

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/27/08	

APPROVED: _____

DATE: _____ TITLE: _____



DESCRIPTION	MATERIAL	FINISH	QTY
BODY	BRASS	NICKEL	1
SHELL	BRASS	NICKEL	1
WASHER	STELL	NICKEL	1
SPRING	SK-5	NICKEL	1
GASKET	RUBBER	RED	1
INSULATOR	TEFLON	NONE	1
RING	BRASS	NICKEL	1
PIN	BARSS	GOLD	1

SPECIFICATIONS:

Electrical:
Nominal Impedance: 50 ohms
Frequency range: 0-4 GHz
Maximum peak voltage: 500V
Insulation resistance: 5000 Mohm min @ 500 VDC
Dielectric withstanding voltage: 1500 VAC rms
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC MALE R/A CRIMP FOR RG174

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				Holes			
INCHES				Holes			
.X ± .10				Ø.X ± .10			
.XX ± .020				Ø.XX ± .015			
.XXX ± .015				Ø.XXX ± .010			
APPROVALS				DATE			
DRAWN				DY			
8/27/08							
CHECKED							
APPROVED							
SIZE				PART NO.			
X				RF1-26-T-02-50			
REV.				-			
REF:				SCALE: NTS			
				SHEET 1 OF 1			