

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/23/14	SLS

6

5

4




3

2

1

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

- Material: Body: Zinc Alloy, Nickel plated
- Contacts: Brass, Gold plated
- Insulator: POM
- Electrical: Nominal Impedance: 75 ohms
- Frequency range: 0–1 GHz
- Working Voltage: 500 VRMS max
- VSWR: 1.3 Max.
- Dielectric Withstanding Voltage: 1500 VRMS min.
- Contact Resistance: 3 Milliohms max. (Center Contact)
- 2 Milliohms max. (Outer Contact)
- Insulator Resistance: 5,000 Megohms min.
- Temperature Range: –55°C to +155°C
- Environmental: Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

BNC CONNECTOR, VERTICAL PCB,
75Ω, MACHINE CONTACT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				HOLES			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	APPROVALS			
DRAWN				AY	1/23/14	TITLE	
CHECKED				NP	1/23/14	BNC CONNECTOR, VERTICAL PCB, 75Ω, MACHINE CONTACT	
APPROVED						SIZE: PART NO.	
						X RF1-95-T-00-75 -MC	
						REV. -	
						SCALE: NTS	
						SHEET 1 OF 1	