

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	9114	RELEASED	11/04/08	
A	9114	REDRAWN	10/18/12	
B		REVISED PIN MATERIAL	8/13/13	
C		ADDED SPEC.	5/28/14	AV/SY



DESCRIPTION	MATERIAL	QTY	FINISH
CHASDSIS	BRASS	1	GOLD
INSULATOR B	TEFLON	1	NONE
PIN	BRASS	1	GOLD
INSULATOR A	TEFLON	1	NONE
WASHER	BRASS	1	GOLD
BODY	BRASS	1	GOLD

SPECIFICATIONS:

Electrical:

Frequency range: 0–18 GHz

Working Voltage: 250 VRMS max.

Dielectric Withstanding Voltage: 750 VRMS max.

Contact Resistance: 6 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5000 Megohms min.

Temperature Rating:

Operating temperature: –65°C to +165°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

SMA JACK R/A PCB MOUNT, FEMALE PIN

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES				APPROVALS			
.X	± .10	Ø.X	± .10	DRAWN	DY	11/04/08	
.XX	± .020	Ø.XX	± .015	CHECKED			
.XXX	± .015	Ø.XXX	± .010	APPROVED			
SIZE PART NO.				REV.			
X RF2-03-1-00-50-G				C			
REF:				SCALE: NTS SHEET 1 OF 1			